

# Eaton XTOE045DCS

Catalog Number: XTOE045DCS

Eaton C440 electronic overload relay, XT IEC Electronic Overload Relay, 9-45A overload range, 55 mm Frame size, NO-NC contact configuration, Direct to contactor mounting, Selectable - 10A, 10, 20, 30 trip type



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton C440 electronic overload relay	XTOE045DCS
<b>UPC</b>	<b>Product Length/Depth</b>
786685416533	1.8 in
<b>Product Height</b>	<b>Product Width</b>
4.3 in	1.42 in
<b>Product Weight</b>	<b>Compliances</b>
0.87 lb	ATEX Compliant
	RoHS Compliant
	CE Marked

## Certifications

UL Listed  
IEC 60947  
CSA Certified  
EN 60947

## Product specifications

### Overload range

9-45A

### Type

Electronic overload relay

### Frame size

55 mm

### Mounting method

Direct

### Contact configuration

NO, NC

### Trip type

Selectable 10 A, class 10 ,20, 30

## Resources

### Brochures

[C440 Electronic Overload Relay](#)

### Specifications and datasheets

[Eaton Specification Sheet - XTOE045DCS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton XTOE045DCS

Catalog Number: XTOE045DCS

Eaton C440 electronic overload relay, XT IEC Electronic Overload Relay, 9-45A overload range, 55 mm Frame size, NO-NC contact configuration, Direct to contactor mounting, Selectable - 10A, 10, 20, 30 trip type



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton C440 electronic overload relay	XTOE045DCS
<b>UPC</b>	<b>Product Length/Depth</b>
786685416533	1.8 in
<b>Product Height</b>	<b>Product Width</b>
4.3 in	1.42 in
<b>Product Weight</b>	<b>Compliances</b>
0.87 lb	ATEX Compliant
	RoHS Compliant
	CE Marked

## Certifications

UL Listed  
IEC 60947  
CSA Certified  
EN 60947

## Product specifications

### Overload range

9-45A

### Type

Electronic overload relay

### Frame size

55 mm

### Mounting method

Direct

### Contact configuration

NO, NC

### Trip type

Selectable 10 A, class 10 ,20, 30

## Resources

### Brochures

[C440 Electronic Overload Relay](#)

### Specifications and datasheets

[Eaton Specification Sheet - XTOE045DCS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)