

Eaton XTOE045DCS

Catalog Number: XTOE045DCS

Eaton C440 electronic overload relay, XT IEC Electronic Overload Relay, 9-45A overload range, 55 mm Frame size, NO-NC contact configuration, Direct to contactor mounting, Selectable - 10A, 10, 20, 30 trip type



General specifications

Product Name	Catalog Number
Eaton C440 electronic overload relay	XTOE045DCS
UPC	Product Length/Depth
786685416533	1.8 in
Product Height	Product Width
4.3 in	1.42 in
Product Weight	Compliances
0.87 lb	ATEX Compliant
	RoHS Compliant
	CE Marked

Certifications

UL Listed
IEC 60947
CSA Certified
EN 60947

defaultTaxonomyAttributeLabel

Overload range

9-45A

Type

Electronic overload relay

Frame size

55 mm

Mounting method

Direct

Contact configuration

NO, NC

Trip type

Selectable 10 A, class 10 ,20, 30

Resources

Brochures

C440 Electronic Overload Relay

Catalogs

Eaton's Volume 5—Motor Control and Protection

Drawings

XTOE045D_S 3D Model Xchange

XTOE045D_S 2D PDF

XTOE045D_S 2D Drawing Xchange

XTOE045D_S 3D Inventor

XTOE045D_S AutoCAD 2D Footprint

XTOE045D_S AutoCAD 2D Footprint (mm)

Installation instructions

XTOE/ZEB IEC Electronic Overload - Self Powered

Specifications and datasheets

Eaton Specification Sheet - XTOE045DCS



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton XTOE045DCS

Catalog Number: XTOE045DCS

Eaton C440 electronic overload relay, XT IEC Electronic Overload Relay, 9-45A overload range, 55 mm Frame size, NO-NC contact configuration, Direct to contactor mounting, Selectable - 10A, 10, 20, 30 trip type



General specifications

Product Name	Catalog Number
Eaton C440 electronic overload relay	XTOE045DCS
UPC	Product Length/Depth
786685416533	1.8 in
Product Height	Product Width
4.3 in	1.42 in
Product Weight	Compliances
0.87 lb	ATEX Compliant
	RoHS Compliant
	CE Marked

Certifications

UL Listed
IEC 60947
CSA Certified
EN 60947

defaultTaxonomyAttributeLabel

Overload range

9-45A

Type

Electronic overload relay

Frame size

55 mm

Mounting method

Direct

Contact configuration

NO, NC

Trip type

Selectable 10 A, class 10 ,20, 30

Resources

Brochures

C440 Electronic Overload Relay

Catalogs

Eaton's Volume 5—Motor Control and Protection

Drawings

XTOE045D_S 3D Model Xchange

XTOE045D_S 2D PDF

XTOE045D_S 2D Drawing Xchange

XTOE045D_S 3D Inventor

XTOE045D_S AutoCAD 2D Footprint

XTOE045D_S AutoCAD 2D Footprint (mm)

Installation instructions

XTOE/ZEB IEC Electronic Overload - Self Powered

Specifications and datasheets

Eaton Specification Sheet - XTOE045DCS



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia