

Eaton XTOE100DCS

Catalog Number: XTOE100DCS

Eaton C440 electronic overload relay, XT IEC Electronic Overload Relay, 20-100A overload range, 55 mm Frame size, NO-NC contact configuration, Direct to contactor mounting, Selectable - 10A, 10, 20, 30 trip type



Photo is representative

General specifications

Product Name	Catalog Number
Eaton C440 electronic overload relay	XTOE100DCS
UPC	Product Length/Depth
786685416557	1.8 in
Product Height	Product Width
4.3 in	1.42 in
Product Weight	Compliances
0.87 lb	CE Marked
	RoHS Compliant
	ATEX Compliant

Certifications

CSA Certified
IEC 60947
EN 60947
UL Listed

defaultTaxonomyAttributeLabel

Overload range

20-100A

Type

Electronic overload relay

Frame size

55 mm

Mounting method

Direct

Contact configuration

NO, NC

Trip type

Selectable 10 A, class 10 ,20, 30

Resources

Brochures

[C440 Electronic Overload Relay](#)

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTOE100D_S AutoCAD 2D Footprint \(mm\)](#)

[XTOE100D_S 3D Inventor](#)

[XTOE100D_S 2D Drawing Xchange](#)

[XTOE100D_S AutoCAD 2D Footprint](#)

[XTOE100D_S 3D Model Xchange](#)

[XTOE100D_S 2D PDF](#)

Installation instructions

[XTOE/ZEB IEC Electronic Overload - Self Powered](#)

Specifications and datasheets

[Eaton Specification Sheet - XTOE100DCS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton XTOE100DCS

Catalog Number: XTOE100DCS

Eaton C440 electronic overload relay, XT IEC Electronic Overload Relay, 20-100A overload range, 55 mm Frame size, NO-NC contact configuration, Direct to contactor mounting, Selectable - 10A, 10, 20, 30 trip type



Photo is representative

General specifications

Product Name	Catalog Number
Eaton C440 electronic overload relay	XTOE100DCS
UPC	Product Length/Depth
786685416557	1.8 in
Product Height	Product Width
4.3 in	1.42 in
Product Weight	Compliances
0.87 lb	CE Marked
	RoHS Compliant
	ATEX Compliant

Certifications

CSA Certified
IEC 60947
EN 60947
UL Listed

defaultTaxonomyAttributeLabel

Overload range

20-100A

Type

Electronic overload relay

Frame size

55 mm

Mounting method

Direct

Contact configuration

NO, NC

Trip type

Selectable 10 A, class 10 ,20, 30

Resources

Brochures

[C440 Electronic Overload Relay](#)

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTOE100D_S AutoCAD 2D Footprint \(mm\)](#)

[XTOE100D_S 3D Inventor](#)

[XTOE100D_S 2D Drawing Xchange](#)

[XTOE100D_S AutoCAD 2D Footprint](#)

[XTOE100D_S 3D Model Xchange](#)

[XTOE100D_S 2D PDF](#)

Installation instructions

[XTOE/ZEB IEC Electronic Overload - Self Powered](#)

Specifications and datasheets

[Eaton Specification Sheet - XTOE100DCS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)