

Eaton XTCE095FS1A

Catalog Number: XTCE095FS1A

Eaton XT IEC contactor, 95A, Side-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 95A, Frame F, 90 mm, 50-60 Hz, 40, 50, 100, 125 hp (3PH @200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing contactor



Photo is representative

General specifications

Product Name

Eaton XT IEC contactor

Catalog Number

XTCE095FS1A

UPC

786685365145

Product Length/Depth

1 in

Product Height

1 in

Product Width

1 in

Product Weight

1 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

CSA Certified

EN 60947

IEC 60947

Product specifications

Amperage Rating

95A

HP rating - max

40, 50, 100, 125 hp (3PH @200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage non-reversing contactor

Frequency rating

50-60 Hz

Frame size

90 mm

Terminals

Screw terminals

Coil

110-120 Vac, 50/60 Hz

Coil voltage

110-120 Vac, 50/60 Hz

Contact configuration

1 NO, 1 NC

Continuous ampere rating

95 A

Series

XT IEC

Operation

Non-reversing

Resources

Specifications and datasheets

[Eaton Specification Sheet - XTCE095FS1A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton XTCE095FS1A

Catalog Number: XTCE095FS1A

Eaton XT IEC contactor, 95A, Side-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 95A, Frame F, 90 mm, 50-60 Hz, 40, 50, 100, 125 hp (3PH @200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing contactor

General specifications



Photo is representative

Product Name

Eaton XT IEC contactor

Catalog Number

XTCE095FS1A

UPC

786685365145

Product Length/Depth

1 in

Product Height

1 in

Product Width

1 in

Product Weight

1 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

CSA Certified

EN 60947

IEC 60947

Product specifications

Amperage Rating

95A

HP rating - max

40, 50, 100, 125 hp (3PH @200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage non-reversing contactor

Frequency rating

50-60 Hz

Frame size

90 mm

Terminals

Screw terminals

Coil

110-120 Vac, 50/60 Hz

Coil voltage

110-120 Vac, 50/60 Hz

Contact configuration

1 NO, 1 NC

Continuous ampere rating

95 A

Series

XT IEC

Operation

Non-reversing

Resources

Specifications and datasheets

[Eaton Specification Sheet - XTCE095FS1A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)