

# Eaton XTCR009B21TD

Catalog Number: XTCR009B21TD

Eaton XT IEC contactor, 9A, 24 Vdc, 2NO-2NO, 9A, Frame B, 45 mm, 0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @115, 230/200, 230, 460, 575 V), Three-pole, Reversing, XT IEC series, Screw terminals, Full voltage reversing contactor

## General specifications



Photo is representative

### Product Name

Eaton XT IEC contactor

### UPC

782116884896

### Product Height

68 mm

### Product Weight

0.28 kg

### Compliances

CE Marked

RoHS Compliant

### Catalog Number

XTCR009B21TD

### Product Length/Depth

117 mm

### Product Width

90 mm

### Warranty

1 year

### Certifications

CSA Certified

EN 60947

UL Listed

IEC 60947

### Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## Product specifications

### Amperage Rating

9A

### HP rating - max

0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @115,230/200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage reversing contactor

### Frame size

45 mm

### Terminals

Screw terminals

### Coil voltage

24 Vdc

### Contact configuration

2 NO, 2 NO

### Continuous ampere rating

9 A

### Series

XT IEC

### Operation

Reversing

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - XTCR009B21TD](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton XTCR009B21TD

Catalog Number: XTCR009B21TD

Eaton XT IEC contactor, 9A, 24 Vdc, 2NO-2NO, 9A, Frame B, 45 mm, 0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @115, 230/200, 230, 460, 575 V), Three-pole, Reversing, XT IEC series, Screw terminals, Full voltage reversing contactor

## General specifications



Photo is representative

### Product Name

Eaton XT IEC contactor

### UPC

782116884896

### Product Height

68 mm

### Product Weight

0.28 kg

### Compliances

CE Marked

RoHS Compliant

### Catalog Number

XTCR009B21TD

### Product Length/Depth

117 mm

### Product Width

90 mm

### Warranty

1 year

### Certifications

CSA Certified

EN 60947

UL Listed

IEC 60947

### Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## Product specifications

### Amperage Rating

9A

### HP rating - max

0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @115,230/200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage reversing contactor

### Frame size

45 mm

### Terminals

Screw terminals

### Coil voltage

24 Vdc

### Contact configuration

2 NO, 2 NO

### Continuous ampere rating

9 A

### Series

XT IEC

### Operation

Reversing

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - XTCR009B21TD](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)