



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## YA27L4BOX 3/0 1H Lug Burndy LLC

Catalog Number	YA27L4BOX
Manufacturer	Burndy LLC
Description	3/0 Awg Cu, One Hole, 3/8 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UI/Csa 90 Up to 35KV, Orange Color Code, 14 Die Index.
Weight per unit	0.0700 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Die Index	14
Material	Copper
Voltage Rating	35

### Material, Color, and Finish

Color Code	ORANGE
------------	--------

### Descriptions

Description	3/0 1H LUG
extra long description	BUR YA27L4BOX 3/0 CU 1-HOLE SHORT 3
Long Description	3/0 AWG CU, One Hole, 3/8 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA 90 Up to 35kV, ORANGE Color Code, 14 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Package: Box, Temperature Rating: 90 DEG C, Wire Strip Length: 1-1/16 IN, Tongue Angle: Straight, Die Index: 14, Finish: Electro-Tin Plated, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W27VT, W27RT Die, (2), X27RT Die, (3), Hydraulic: BCT500HS, Y500CTHS Tool, W27VT, W27RT Die, (2), X27RT Die, (3), Y35, Y39, Y750, PAT750 Tool, U27RT Die, (1), Y46 Tool, U27RT Die With PUADP-1

### Manufacturer Information

Brand	BURNDY
GTIN	00781810554005
Manufacturers Part Number	YA27L4BOX
UPC	781810554005

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel, Tin Plated



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.07

## Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B