

# PUSH BUTTONS

## Explosionproof & Dust-Tight Push Buttons

**Class I, Groups B, C & D**  
**Class II, Groups E, F & G**  
**NEMA 3, 4, 7 & 9**

### FEATURES

- All operators are die cast aluminum alloy. The barrels are all 3/4" NPSM thread. Maximum installation thickness 1 3/4" panel mount, 3/4" surface mount.
- Black molded nylon buttons. The exposed metal parts are black anodized aluminum. For color coding we will furnish at no additional cost the following color combinations: Red buttons with red metal caps and green buttons with green metal caps. Metal caps are also available in blue, gold or clear with black buttons. Specify colors required.
- Red Mushroom head buttons are 1 3/4" diameter anodized aluminum. Also available in black or green.
- XHPBPL has padlock attachment on top of cap allowing operator to be locked with the push button depressed.
- For use with BT contact blocks. Contact blocks can be stacked for multiple circuits. Contact blocks are not included with the operators.
- XHPPM/XHPPMS require 2" minimum spacing.
- XHPB pushbuttons are momentary.
- XHPP pushbuttons are maintained.

### FOR USE WITH SERIES BT CONTACT BLOCKS

| Catalog # | Operator Description              | Weight (lbs.) |
|-----------|-----------------------------------|---------------|
| XHPB      | Panel Mount                       | 1/2           |
| XHPBS     | Surface Mount                     | 1/2           |
| XHPBM     | Red Mushroom Head, Panel Mount    | 1/2           |
| XHPBMS    | Red Mushroom Head, Surface Mount  | 1/2           |
| XHPBPL    | W/Padlock devices, Panel Mount    | 3/4           |
| XHPBSPL   | W/Padlock devices, Surface Mount  | 3/4           |
| XHPPM*    | Push/Pull switches, Panel Mount   | 3/4           |
| XHPPMS*   | Push/Pull switches, Surface Mount | 3/4           |

\*Type BT1 contact blocks are included

### LEGEND PLATES AT END OF SECTION

**NOTE** For extremely wet-dirty location applications, XHPB and XHPBS series are available to be used with protective boots.



XHPB



XHPBS



XHPBM



XHPBMS



XHPPM



XHPPMS



XHPBPL



XHPBSPL

# PUSH BUTTONS

## Explosionproof & Dust-Tight Push Buttons

**Class I, Groups B, C & D  
Class II, Groups E, F & G  
NEMA 3, 4, 7 & 9**

### FEATURES

- All operators are die cast aluminum alloy. The barrels are all 3/4" NPSM thread. Maximum installation thickness 1 3/4" panel mount, 3/4" surface mount.
- Black molded nylon buttons. The exposed metal parts are black anodized aluminum. For color coding we will furnish at no additional cost the following color combinations: Red buttons with red metal caps and green buttons with green metal caps. Metal caps are also available in blue, gold or clear with black buttons. Specify colors required.
- Red Mushroom head buttons are 1 3/4" diameter anodized aluminum. Also available in black or green.
- XHPBPL has padlock attachment on top of cap allowing operator to be locked with the push button depressed.
- For use with BT contact blocks. Contact blocks can be stacked for multiple circuits. Contact blocks are not included with the operators.
- XHPPM/XHPPMS require 2" minimum spacing.
- XHPB pushbuttons are momentary.
- XHPP pushbuttons are maintained.

| FOR USE WITH SERIES BT CONTACT BLOCKS |                                   |               |
|---------------------------------------|-----------------------------------|---------------|
| Catalog #                             | Operator Description              | Weight (lbs.) |
| XHPB                                  | Panel Mount                       | 1/2           |
| XHPBS                                 | Surface Mount                     | 1/2           |
| XHPBM                                 | Red Mushroom Head, Panel Mount    | 1/2           |
| XHPBMS                                | Red Mushroom Head, Surface Mount  | 1/2           |
| XHPBPL                                | W/Padlock devices, Panel Mount    | 3/4           |
| XHPBSPL                               | W/Padlock devices, Surface Mount  | 3/4           |
| XHPPM*                                | Push/Pull switches, Panel Mount   | 3/4           |
| XHPPMS*                               | Push/Pull switches, Surface Mount | 3/4           |

\*Type BT1 contact blocks are included

### LEGEND PLATES AT END OF SECTION

**NOTE** For extremely wet-dirty location applications, XHPB and XHPBS series are available to be used with protective boots.



XHPB



XHPBS



XHPBM



XHPBMS



XHPPM



XHPPMS



XHPBPL



XHPBSPL