

Guarded Pilot Lights for Group B Applications



**XL Long Series
(Panel Mount)**



**XLS Short Series
(Surface Mount)**



Replacement Cap

**Class I, Groups B, C & D
Class II, Groups E, F & G
NEMA 3, 4, 7 & 9**

FEATURES

- Explosionproof pilot lights are suitable for panel or surface mount applications.
- Sealed construction and can be relamped from the front by removal of lens cap.
- Made with 3/4" NPSM threads.
- 8" flexible leads, other lengths on special order, or screw terminal (suffix T).
- All lens caps are black anodized aluminum finish.
- **Maximum installation thickness:** 1 13/16" on Long Series, 5/8" on Short Series.
- **Standard Series**-Equipped with candelabra base receptacles and 6 watt 120 volt 6S6 Clear 1500 hr. avg. lamps. Also available with 6, 12, 24, 30, 50, 75 and 135 volt lamps. Specify voltage desired.
- **Slide Base Series**-Equipped with slide base receptacles and 120 volt 5000 hr. avg. lamps with slide base. Also available with 6, 12, 24, 48 and 60 volt lamps. Specify voltage desired.

STANDARD SERIES

| Panel Mount Cat # | Surface Mount Cat # | Description | Weight (lbs.) |
|-------------------|---------------------|-------------|---------------|
| XLA-GH | XLSA-GH | Amber Lens | 1/2 |
| XLB-GH | XLSB-GH | Blue Lens | 1/2 |
| XLC-GH | XLSC-GH | Clear Lens | 1/2 |
| XLG-GH | XLSG-GH | Green Lens | 1/2 |
| XLR-GH | XLSR-GH | Red Lens | 1/2 |
| XLW-GH | XLSW-GH | White Lens | 1/2 |

SLIDE BASE SERIES

| Panel Mount Cat # | Surface Mount Cat # | Description | Weight (lbs.) |
|-------------------|---------------------|-------------|---------------|
| XLAS-GH | XLSAS-GH | Amber Lens | 1/2 |
| XLBS-GH | XLSBS-GH | Blue Lens | 1/2 |
| XLCS-GH | XLSCS-GH | Clear Lens | 1/2 |
| XLGS-GH | XLSGS-GH | Green Lens | 1/2 |
| XLRS-GH | XLSRS-GH | Red Lens | 1/2 |
| XLWS-GH | XLSWS-GH | White Lens | 1/2 |

*Add suffix T to P/N for screw terminal (Example: XLAST-GH)

REPLACEMENT CAP

| Cat # | Description | Weight (lbs.) |
|---------|-------------|---------------|
| XLA-GCH | Amber Lens | 1/8 |
| XLB-GCH | Blue Lens | 1/8 |
| XLC-GCH | Clear Lens | 1/8 |
| XLG-GCH | Green Lens | 1/8 |
| XLR-GCH | Red Lens | 1/8 |
| XLW-GCH | White Lens | 1/8 |