



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## YS28 Hylink Splice Long Barrel

*Burndy LLC*

Catalog Number	YS28
Manufacturer	Burndy LLC
Description	4/0 Awg Cu, Long Barrel, Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, Purple Color Code, 15 Die Index.
Weight per unit	0.1500 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Die Index	15
Material	Copper
Voltage Rating	35

### Material, Color, and Finish

Color Code	PURPLE
Finish	Tin-Plated

### Descriptions

Description	HYLINK SPLICE LONG BARREL
extra long description	BUR YS28 HYLINK-SPLICE LNG BARREL
Long Description	4/0 AWG CU, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, PURPLE Color Code, 15 Die Index.
Product Type	Splice
Special Features	Features: UL Listed 90 DEG C, 600 Volts to 35 kV, Long Barrel Length: Ideal For 600 Volt Heavy Duty Applications, Also May Be Used At Higher Voltages Up To 35KV, Four (4) Center Conductor Stops: Provides A Center Wire Stop For Proper Conductor Insertion, High Pull Out Force: Provides Added Security For Much Greater Mechanical And Electrical Properties, Oil Stop: No, Dieless Tools (number Of Crimps): Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (2), Color Code: Purple, Tapered End: No, Die Index: 15 Element A, Wir

### Manufacturer Information

Brand	BURNDY
GTIN	00781810507803
Manufacturers Part Number	YS28
UPC	781810507803

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	YS, Long Barrel



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.15

## Uses, Certifications, and Standards

Application	Wire Splice
standard	UL 486A-486B