

Specifications

Photo is representative

Eaton XTOE100DCS

Eaton C440 electronic overload relay, XT IEC Electronic Overload Relay, 20-100A overload range, 55 mm Frame size, NO-NC contact configuration, Direct to contactor mounting, Selectable - 10A, 10, 20, 30 trip type

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton C440 electronic overload relay |
| CATALOG NUMBER | XTOE100DCS |
| UPC | 786685416557 |
| PRODUCT LENGTH/DEPTH | 1.8 in |
| PRODUCT HEIGHT | 4.3 in |
| PRODUCT WIDTH | 1.42 in |
| PRODUCT WEIGHT | 0.87 lb |
| COMPLIANCES | CE Marked RoHS Compliant ATEX Compliant |
| CERTIFICATIONS | CSA Certified IEC 60947 EN 60947 UL Listed |

Product specifications

| | |
|-----------------------|--------------------------------------|
| OVERLOAD RANGE | 20-100A |
| TYPE | Electronic overload relay |
| FRAME SIZE | 55 mm |
| MOUNTING METHOD | Direct |
| CONTACT CONFIGURATION | NO, NC |
| TRIP TYPE | Selectable 10 A, class 10 ,20, 30 |

Resources

| | |
|-------------------------------|---|
| BROCHURES | C440 Electronic Overload Relay |
| CATALOGS | Motor Control and Protection, NEMA Contactors and Starters, Volume 5, Tab 2 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - XTOE100DCS |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Photo is representative

Eaton XTOE100DCS

Eaton C440 electronic overload relay, XT IEC Electronic Overload Relay, 20-100A overload range, 55 mm Frame size, NO-NC contact configuration, Direct to contactor mounting, Selectable - 10A, 10, 20, 30 trip type

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton C440 electronic overload relay |
| CATALOG NUMBER | XTOE100DCS |
| UPC | 786685416557 |
| PRODUCT LENGTH/DEPTH | 1.8 in |
| PRODUCT HEIGHT | 4.3 in |
| PRODUCT WIDTH | 1.42 in |
| PRODUCT WEIGHT | 0.87 lb |
| COMPLIANCES | CE Marked RoHS Compliant ATEX Compliant |
| CERTIFICATIONS | CSA Certified IEC 60947 EN 60947 UL Listed |

Product specifications

| | |
|-----------------------|--------------------------------------|
| OVERLOAD RANGE | 20-100A |
| TYPE | Electronic overload relay |
| FRAME SIZE | 55 mm |
| MOUNTING METHOD | Direct |
| CONTACT CONFIGURATION | NO, NC |
| TRIP TYPE | Selectable 10 A, class 10 ,20, 30 |

Resources

| | |
|-------------------------------|---|
| BROCHURES | C440 Electronic Overload Relay |
| CATALOGS | Motor Control and Protection, NEMA Contactors and Starters, Volume 5, Tab 2 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - XTOE100DCS |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

