

# Eaton XTSC001BBA

Catalog Number: XTSC001BBA

Eaton XT IEC motor control, Full Voltage Non-Reversing, Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 3.5A, Factory-assembled, B-frame, 380V/50 Hz, 440V/60 Hz coil, 1NO-1NC, 3-phase



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton XT IEC motor control	XTSC001BBA
<b>UPC</b>	<b>Product Length/Depth</b>
782116602384	3.77 in
<b>Product Height</b>	<b>Product Width</b>
6 in	1.77 in
<b>Product Weight</b>	<b>Compliances</b>
0.001 lb	CE Marked DIN VDE 0600

## Certifications

IEC 60947  
UL Listed file E245398  
CSA file No. 229767, Class 3211-05  
UL 508

## defaultTaxonomyAttributeLabel

### Amperage Rating

1A

### Frame size

45 mm

### Coil

110-120 Vac, 50/60 Hz

## Resources

### Brochures

[XT IEC Power Control](#)

### Catalogs

[Motor Control and Protection](#)

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[XTSC\\_BB 2D PDF](#)

[XTSC\\_BB 2D Drawing Xchange](#)

[XTSC\\_BB AutoCAD 2D Footprint \(mm\)](#)

[XTSC\\_BB 3D Model Xchange](#)

[XTSC\\_BB 3D Inventor](#)

[XTSC\\_BB AutoCAD 2D Footprint](#)

### Specifications and datasheets

[Eaton Specification Sheet - XTSC001BBA](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton XTSC001BBA

Catalog Number: XTSC001BBA

Eaton XT IEC motor control, Full Voltage Non-Reversing, Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 3.5A, Factory-assembled, B-frame, 380V/50 Hz, 440V/60 Hz coil, 1NO-1NC, 3-phase



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton XT IEC motor control	XTSC001BBA
<b>UPC</b>	<b>Product Length/Depth</b>
782116602384	3.77 in
<b>Product Height</b>	<b>Product Width</b>
6 in	1.77 in
<b>Product Weight</b>	<b>Compliances</b>
0.001 lb	CE Marked DIN VDE 0600

## Certifications

IEC 60947  
UL Listed file E245398  
CSA file No. 229767, Class 3211-05  
UL 508

## defaultTaxonomyAttributeLabel

### Amperage Rating

1A

### Frame size

45 mm

### Coil

110-120 Vac, 50/60 Hz

## Resources

### Brochures

[XT IEC Power Control](#)

### Catalogs

[Motor Control and Protection](#)

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[XTSC\\_BB 2D PDF](#)

[XTSC\\_BB 2D Drawing Xchange](#)

[XTSC\\_BB AutoCAD 2D Footprint \(mm\)](#)

[XTSC\\_BB 3D Model Xchange](#)

[XTSC\\_BB 3D Inventor](#)

[XTSC\\_BB AutoCAD 2D Footprint](#)

### Specifications and datasheets

[Eaton Specification Sheet - XTSC001BBA](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)