



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YA2C2LN 2AWG Cop 2H Lug *Burndy LLC*

Catalog Number	YA2C2LN
Manufacturer	Burndy LLC
Description	2 Awg Cu, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, Brown Color Code, 10 Die Index.
Weight per unit	0.0900 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Bolt Size	1/2 in
Die Index	10
Material	Copper
Voltage Rating	35

Material, Color, and Finish

Color Code	BROWN
------------	-------

Descriptions

Description	2AWG COP 2H LUG
extra long description	BUR YA2C2LN CULUG-2STR-SHORT-(2)NEM
Long Description	2 AWG CU, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, Brown Color Code, 10 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Wire Strip Length: 15/16 IN, Die Index: 10, Temperature Rating: 90 DEG C, Tongue Angle: Straight, Finish: Electro-Tin Plated, Color Code: Brown, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W2CVT, W2CRT, X2CRT Die, (1), Hydraulic: BCT500HS, Y500CTHS Tool, W2CVT, W2CRT, X2CRT Die, (1), Y35, Y39, Y750, PAT750 Tool, U2CRT Die, (1), Y46 Tool, U2CRT Die With PUADP-1 Adapter, (1).

Manufacturer Information

Brand	BURNDY
GTIN	00781810500767
Manufacturers Part Number	YA2C2LN
UPC	781810500767

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel, Tin Plated



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.09

Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B