



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YAEV18 22-18AWG Ins Ring Lug

Burndy LLC

Catalog Number	YAEV18
Manufacturer	Burndy LLC
Description	Insulug Nylon Insulated Compression Ring Tongue Terminal; Stud: #8 - #10; Length: .91"; Width: .31"; 600 V Max.
Weight per unit	0.0020 (lbs/each)
Product Category	Large Terminals & Connectors

Features

insulation	Y
Insulation Type	Nylon
Material	Copper
pallet quantity	99999

Material, Color, and Finish

Color Code	RED
------------	-----

Descriptions

Description	22-18AWG INS RING LUG
extra long description	BUR YAEV18 22-18 NYL HVY DTY RING 8
Long Description	INSULUG Nylon Insulated Compression Ring Tongue Terminal; Stud: #8 - #10; Length: .91"; Width: .31"; 600 V Max.
Product Type	Terminal
Special Features	Features: The INSULUG Type YAEV Is Designed For Very Demanding High Vibration Applications Encountered In Aircraft And Aboard Ships As Well As Motor Lead Applications In Hospitals, Industrials And Generating Plants, The Nylon Insulated Seamless, Electrolytic Copper Barrel With Double Thick Tongue Provides An Extra Strong Insulated Connection, The Terminal Is Rated 105 DEG C And Meets SAE-AS7928 Requirements, Double Thick Tongue: Provides Maximum Reliability And Electrical Capacity Plus An Extra Strong Term

Manufacturer Information

Brand	BURNDY
GTIN	00781810024812
Manufacturers Part Number	YAEV18
UPC	781810024812

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	YAEV, Heavy Duty



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1000
Weight Per each	0.002

Uses, Certifications, and Standards

Application	For High Vibration Applications Encountered In Aircraft And Aboard Ships As Well As Motor Lead Applications In Hospitals, Industrials And Generating Plants
standard	UL486;Military Specified (Mil-Spec)