

BURNDY Catalog Number
UPC Number

YAV6CL
7818100255988
6AWG HVYDTY RING 1/4
STU,1.31 IN L
Active

Description
Status

Web Use
BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	1.31
Tongue Type	Ring
Pad Width (in)	0.48
Strip Length	1/2

General

Product Description
Copper Compression Lug, Ring Tongue, 1 Hole w/ Inspection Hole, AN-5 Flex/ AN-6 Flex, 1/4" Stud, Short Barrel, Tin Plated

Conductor(s)

Aircraft Cable Size (Range)	AN 6
Copper Solid Size (Range)	6
Navy Cable Size (Range)	N/A
Copper Stranded (Range)	6

Physical

Type of Plating	Tin - Electro Plated
Connector Type	Terminal - Ring
Plated (Yes or No)	Y

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
Mil-Spec Class Code	Class 1
CULUS	N
Industry Standards	UL467, Military Specified (Mil-Spec)

Documentation

For further technical assistance, please contact us


BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175



BURNDY Catalog Number
UPC Number

YAV6CL
7818100255988
6AWG HVYDTY RING 1/4
STU,1.31 IN L
Active

Description
Status

Web Use
BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	1.31
Tongue Type	Ring
Pad Width (in)	0.48
Strip Length	1/2

General

Product Description
Copper Compression Lug, Ring Tongue, 1 Hole w/ Inspection Hole, AN-5 Flex/ AN-6 Flex, 1/4" Stud, Short Barrel, Tin Plated

Conductor(s)

Aircraft Cable Size (Range)	AN 6
Copper Solid Size (Range)	6
Navy Cable Size (Range)	N/A
Copper Stranded (Range)	6

Physical

Type of Plating	Tin - Electro Plated
Connector Type	Terminal - Ring
Plated (Yes or No)	Y

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
Mil-Spec Class Code	Class 1
CULUS	N
Industry Standards	UL467, Military Specified (Mil-Spec)

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175