



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## YS26LBOX 1/0AWG Butt Splice Black

Burndy LLC

Catalog Number	YS26LBOX
Manufacturer	Burndy LLC
Description	2/0 Awg Cu, Standard Barrel, Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, Black Color Code, 13 Die Index.
Weight per unit	0.0600 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Die Index	13
Material	Copper
Voltage Rating	35

### Material, Color, and Finish

Color Code	BLACK
Finish	Tin-Plated

### Descriptions

Description	1/0AWG BUTT SPLICE BLACK
extra long description	BUR YS26LBOX 2/0 STR. CU. BUTT SPLI
Long Description	2/0 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kv, BLACK Color Code, 13 Die Index.
Product Type	Splice
Special Features	Features: Standard Barrel Length: Ideal For Limited Space Applications While Providing Ample Barrel Length For Proper Crimp, Four (4) Center Conductor Stops: Provides A Center Wire Stop For Proper Conductor Insertion, Dieless Tools (number Of Crimps): Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (1), Tapered End: No, Oil Stop: No, Color Code: Black, Die Index: 13 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD7-34R Tool, W26VT Die, (2), MD6, OUR840 Tool, X26RT Die, (2), Y35, Y39,

### Manufacturer Information

Brand	BURNDY
GTIN	00781810556252
Manufacturers Part Number	YS26LBOX
UPC	781810556252

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	YS-L, Standard Barrel



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.06

## Uses, Certifications, and Standards

Application	Wire Splice
standard	UL 486A-486B