



SAFETY DATA SHEET

1. Identification

Product identifier	Red Grease
Other means of identification	
Product Code	No. 03079 (Item# 1003339)
Recommended use	Lubricating grease
Recommended restrictions	None known.
Manufacturer/Importer/Supplier/Distributor information	
Manufactured or sold by:	
Company name	CRC Industries, Inc.
Address	885 Louis Dr. Warminster, PA 18974 US
Telephone	
General Information	215-674-4300
Technical Assistance	800-521-3168
Customer Service	800-272-4620
24-Hour Emergency	800-424-9300 (US)
(CHEMTREC)	703-527-3887 (International)
Website	www.crcindustries.com

2. Hazard(s) identification

Physical hazards	Flammable aerosols Gases under pressure	Category 1 Liquefied gas
Health hazards	Skin corrosion/irritation Specific target organ toxicity, single exposure Aspiration hazard	Category 2 Category 3 narcotic effects Category 1
Environmental hazards	Hazardous to the aquatic environment, acute hazard Hazardous to the aquatic environment, long-term hazard	Category 2 Category 3
OSHA defined hazards	Not classified.	

Label elements



Signal word	Danger
Hazard statement	Extremely flammable aerosol. Contains gas under pressure; may explode if heated. May be fatal if swallowed and enters airways. Causes skin irritation. May cause drowsiness or dizziness. Toxic to aquatic life. Harmful to aquatic life with long lasting effects.
Precautionary statement	
Prevention	Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use. Do not apply while equipment is energized. Extinguish all flames, pilot lights, and heaters. Vapors will accumulate readily and may ignite. Use only with adequate ventilation; maintain ventilation during use and until all vapors are gone. Open doors and windows or use other means to ensure a fresh air supply during use and while product is drying. If you experience any symptoms listed on this label, increase ventilation or leave the area. Avoid breathing mist or vapor. Wash thoroughly after handling. Wear protective gloves. Avoid release to the environment.

Response	If swallowed: Immediately call a poison center/doctor. Do NOT induce vomiting. If on skin: Wash with plenty of water. If skin irritation occurs: Get medical advice/attention. Take off contaminated clothing and wash before reuse. If inhaled: Remove person to fresh air and keep comfortable for breathing. Call a poison center/doctor if you feel unwell.
Storage	Store in a well-ventilated place. Store locked up. Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. Exposure to high temperature may cause can to burst.
Disposal	Dispose of contents/container in accordance with local/regional/national regulations.
Hazard(s) not otherwise classified (HNOC)	None known.
Supplemental information	None.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
heptane, branched, cyclic and linear		426260-76-6	40 - 50
mineral oil		Mixture	30 - 40
propane		74-98-6	10 - 20
aluminum hydroxide benzoate stearate		54326-11-3	5 - 10

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
Skin contact	Remove contaminated clothing. Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention. Wash contaminated clothing before reuse.
Eye contact	Rinse with water. Get medical attention if irritation develops and persists.
Ingestion	Call a physician or poison control center immediately. Rinse mouth. Do not induce vomiting. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs.
Most important symptoms/effects, acute and delayed	Aspiration may cause pulmonary edema and pneumonitis. May cause drowsiness and dizziness. Headache. Nausea, vomiting. Skin irritation. May cause redness and pain.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

5. Fire-fighting measures

Suitable extinguishing media	Water fog. Foam. Dry chemical powder. Dry chemicals. Carbon dioxide (CO2).
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	Contents under pressure. Pressurized container may rupture when exposed to heat or flame. During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.
Fire fighting equipment/instructions	In case of fire: Stop leak if safe to do so. Move containers from fire area if you can do so without risk. Cool containers exposed to heat with water spray and remove container, if no risk is involved. Containers should be cooled with water to prevent vapor pressure build up.
General fire hazards	Extremely flammable aerosol. Contents under pressure. Pressurized container may rupture when exposed to heat or flame.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Keep out of low areas. Many gases are heavier than air and will spread along ground and collect in low or confined areas (sewers, basements, tanks). Wear appropriate protective equipment and clothing during clean-up. Avoid breathing mist or vapor. Emergency personnel need self-contained breathing equipment. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ventilate closed spaces before entering them. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.

Methods and materials for containment and cleaning up

Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil, etc.) away from spilled material. This product is miscible in water. This material is classified as a water pollutant under the Clean Water Act and should be prevented from contaminating soil or from entering sewage and drainage systems which lead to waterways. Stop the flow of material, if this is without risk. Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination. For waste disposal, see section 13 of the SDS.

Environmental precautions

Avoid release to the environment. Inform appropriate managerial or supervisory personnel of all environmental releases. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling

Pressurized container: Do not pierce or burn, even after use. Do not use if spray button is missing or defective. Do not spray on a naked flame or any other incandescent material. Do not smoke while using or until sprayed surface is thoroughly dry. Do not cut, weld, solder, drill, grind, or expose containers to heat, flame, sparks, or other sources of ignition. Use caution around energized equipment. The metal container will conduct electricity if it contacts a live source. This may result in injury to the user from electrical shock and/or flash fire. Avoid breathing mist or vapor. Avoid contact with eyes, skin, and clothing. Avoid prolonged or repeated contact with skin. Avoid prolonged exposure. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Wash hands thoroughly after handling. Avoid release to the environment. Observe good industrial hygiene practices. For product usage instructions, see the product label.

Conditions for safe storage, including any incompatibilities

Level 3 Aerosol.

Pressurized container. Protect from sunlight and do not expose to temperatures exceeding 50°C/122 °F. Do not puncture, incinerate or crush. Do not handle or store near an open flame, heat or other sources of ignition. This material can accumulate static charge which may cause spark and become an ignition source. Store in a well-ventilated place. Stored containers should be periodically checked for general condition and leakage. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection

Occupational exposure limits

U.S. - OSHA Components

Components	Type	Value
mineral oil	TWA	5 mg/m ³

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value
propane (CAS 74-98-6)	PEL	1800 mg/m ³ 1000 ppm

ACGIH

Components

Components	Type	Value	Form
mineral oil	TWA	5 mg/m ³	Inhalable fraction

US. ACGIH Threshold Limit Values

Components	Type	Value	Form
aluminum hydroxide benzoate stearate (CAS 54326-11-3)	TWA	1 mg/m ³	Respirable fraction.

U.S. - NIOSH

Components

Components	Type	Value	Form
mineral oil	STEL	10 mg/m ³	Mist
	TWA	5 mg/m ³	Mist

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
propane (CAS 74-98-6)	TWA	1800 mg/m ³ 1000 ppm
Biological limit values	No biological exposure limits noted for the ingredient(s).	
Appropriate engineering controls	Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Eye wash facilities and emergency shower should be available when handling this product.	
Individual protection measures, such as personal protective equipment		
Eye/face protection	Wear safety glasses with side shields (or goggles).	
Skin protection		
Hand protection	Wear protective gloves such as: Nitrile. Neoprene.	
Other	Wear appropriate chemical resistant clothing.	
Respiratory protection	If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels.	
Thermal hazards	Wear appropriate thermal protective clothing, when necessary.	
General hygiene considerations	When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.	

9. Physical and chemical properties

Appearance

Physical state	Liquid.
Form	Aerosol.
Color	Red.
Odor	Solvent.
Odor threshold	Not available.
pH	Not available.
Melting point/freezing point	Not available.
Initial boiling point and boiling range	175 °F (79.4 °C)
Flash point	< 20 °F (< -6.7 °C)
Evaporation rate	Fast.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	1.2
Flammability limit - upper (%)	6.7
Vapor pressure	2544.3 hPa estimated
Vapor density	> 1 (air = 1)
Relative density	0.67 estimated
Solubility(ies)	
Solubility (water)	Slightly soluble.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	Not available.
Decomposition temperature	Not available.
Percent volatile	94.4 % estimated

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Conditions to avoid	Heat, flames and sparks. Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents.
Hazardous decomposition products	No hazardous decomposition products are known.

11. Toxicological information

Information on likely routes of exposure

Inhalation	May cause drowsiness and dizziness. Headache. Nausea, vomiting. Prolonged inhalation may be harmful.
Skin contact	Causes skin irritation.
Eye contact	Direct contact with eyes may cause temporary irritation.
Ingestion	Droplets of the product aspirated into the lungs through ingestion or vomiting may cause a serious chemical pneumonia.

Symptoms related to the physical, chemical and toxicological characteristics Aspiration may cause pulmonary edema and pneumonitis. May cause drowsiness and dizziness. Headache. Nausea, vomiting. Skin irritation. May cause redness and pain.

Information on toxicological effects

Acute toxicity May be fatal if swallowed and enters airways.

Components	Species	Test Results
-------------------	----------------	---------------------

heptane, branched, cyclic and linear (CAS 426260-76-6)

Acute

Dermal

LD50	Rabbit	> 2000 mg/kg
------	--------	--------------

Inhalation

LC50	Rat	> 60 mg/l, 4 hours
------	-----	--------------------

Oral

LD50	Rat	> 5000 mg/kg
------	-----	--------------

mineral oil

Acute

Dermal

LD50	Rabbit	> 2000 mg/kg
------	--------	--------------

Inhalation

Vapor

LC50	Rat	2180 mg/kg, 4 hours
------	-----	---------------------

Oral

LD50	Rat	> 5000 mg/kg
------	-----	--------------

propane (CAS 74-98-6)

Acute

Dermal

LD50	Rabbit	> 5000 mg/kg
------	--------	--------------

Skin corrosion/irritation Causes skin irritation.

Serious eye damage/eye irritation Direct contact with eyes may cause temporary irritation.

Respiratory or skin sensitization

Respiratory sensitization Not a respiratory sensitizer.

Skin sensitization This product is not expected to cause skin sensitization.

Germ cell mutagenicity No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.

Carcinogenicity Not classifiable as to carcinogenicity to humans.

IARC Monographs. Overall Evaluation of Carcinogenicity

Not listed.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)

Not regulated.

US. National Toxicology Program (NTP) Report on Carcinogens

Not listed.

Reproductive toxicity This product is not expected to cause reproductive or developmental effects.

Specific target organ toxicity - single exposure May cause drowsiness and dizziness.

Specific target organ toxicity - repeated exposure Not classified.

Aspiration hazard May be fatal if swallowed and enters airways. If aspirated into lungs during swallowing or vomiting, may cause chemical pneumonia, pulmonary injury or death.

Chronic effects Prolonged inhalation may be harmful.

12. Ecological information

Ecotoxicity Toxic to aquatic life. Harmful to aquatic life with long lasting effects.

Components	Species	Test Results
heptane, branched, cyclic and linear (CAS 426260-76-6)		
Aquatic		
<i>Acute</i>		
Crustacea	EC50	Water flea (Daphnia magna) 1.5 mg/l, 48 hours
mineral oil		
Aquatic		
<i>Acute</i>		
Crustacea	EC50	Water flea (Daphnia magna) > 10000 mg/l, 48 hours
Fish	LC50	Fathead minnow (Pimephales promelas) > 100 mg/l, 96 hours

Persistence and degradability No data is available on the degradability of any ingredients in the mixture.

Bioaccumulative potential

Partition coefficient n-octanol / water (log Kow)	
propane	2.36

Mobility in soil No data available.

Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal instructions If discarded, this product is considered a RCRA ignitable waste, D001. Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Contents under pressure. Do not puncture, incinerate or crush. Dispose in accordance with all applicable regulations.

Hazardous waste code D001: Waste Flammable material with a flash point <140 F

Contaminated packaging Empty containers should be taken to an approved waste handling site for recycling or disposal. Since emptied containers may retain product residue, follow label warnings even after container is emptied.

14. Transport information

DOT

UN number	UN1950
UN proper shipping name	Aerosols, flammable, Limited Quantity
Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
Label(s)	2.1
Packing group	Not applicable.
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
Special provisions	N82

Packaging exceptions 306
Packaging non bulk 304
Packaging bulk None

IATA

UN number UN1950
UN proper shipping name Aerosols, flammable, Limited Quantity
Transport hazard class(es)
Class 2.1
Subsidiary risk -
Packing group Not applicable.
ERG Code 10L
Special precautions for user Read safety instructions, SDS and emergency procedures before handling.
Other information
Passenger and cargo aircraft Allowed with restrictions.
Cargo aircraft only Allowed with restrictions.

IMDG

UN number UN1950
UN proper shipping name AEROSOLS, Limited Quantity
Transport hazard class(es)
Class 2
Subsidiary risk -
Packing group Not applicable.
Environmental hazards
Marine pollutant No.
EmS F-D, S-U
Special precautions for user Read safety instructions, SDS and emergency procedures before handling.

15. Regulatory information

US federal regulations This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)

Not regulated.

US EPCRA (SARA Title III) Section 313 - Toxic Chemical: Listed substance

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

CERCLA Hazardous Substances: Reportable quantity

Not listed.

Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

propane (CAS 74-98-6)

Safe Drinking Water Act (SDWA) Not regulated.

Food and Drug Administration (FDA) Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Classified hazard categories Flammable (gases, aerosols, liquids, or solids)
 Gas under pressure
 Acute toxicity (any route of exposure)
 Skin corrosion or irritation
 Specific target organ toxicity (single or repeated exposure)
 Aspiration hazard
 Hazard not otherwise classified (HNOC)

SARA 302 Extremely hazardous substance

Not listed.

SARA 313 (TRI reporting)

Not regulated.

US state regulations**US. New Jersey Worker and Community Right-to-Know Act**

propane (CAS 74-98-6)

US. Massachusetts RTK - Substance List

propane (CAS 74-98-6)

US. Pennsylvania Worker and Community Right-to-Know Law

propane (CAS 74-98-6)

US. Rhode Island RTK

propane (CAS 74-98-6)

California Proposition 65**WARNING:** Cancer - www.P65Warnings.ca.gov**California Proposition 65 - CRT: Listed date/Carcinogenic substance**

C.I. Solvent Yellow 14 (CAS 842-07-9)	Listed: May 15, 1998
C.I. Solvent Yellow 3 (CAS 97-56-3)	Listed: July 1, 1987
ethylbenzene (CAS 100-41-4)	Listed: June 11, 2004

Volatile organic compounds (VOC) regulations**EPA****VOC content (40 CFR 51.100(s))** 63 %**Consumer products (40 CFR 59, Subpt. C)** Not regulated**State****Consumer products** Not regulated**VOC content (CA)** 63 %**VOC content (OTC)** 63 %**International Inventories**

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	No
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	No
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	No
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	No
New Zealand	New Zealand Inventory	No
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	No
Taiwan	Taiwan Toxic Chemical Substances (TCS)	No

Country(s) or region	Inventory name	On inventory (yes/no)*
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)
A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date	07-16-2015
Revision date	01-24-2018
Prepared by	Allison Yoon
Version #	03
HMIS® ratings	Health: 2 Flammability: 4 Physical hazard: 0 Personal protection: B
NFPA ratings	Health: 2 Flammability: 4 Instability: 0

NFPA ratings



Disclaimer

The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC's knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries, Inc..

Revision information

This document has undergone significant changes and should be reviewed in its entirety.