

## Accessories

### TS 35X7.5/LL 2M/ST/ZN

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



### Building installation wiring

For building installations, we offer a complete system that revolves around the 10×3 copper rail and comprises perfectly coordinated components: from installation terminal blocks, neutral conductor terminal blocks and distribution terminal blocks to comprehensive accessories such as busbars and busbar holders.

### General ordering data

|            |  |
|------------|--|
| Type       | TS 35X7.5/LL 2M/ST/ZN  |
| Order No.  | <a href="#">051450000</a>  |
| Version    | Mounting rail, TS 35, TS 35 x 7.5, with slot, Steel, galvanized, chromium-plated |
| GTIN (EAN) | 4008190046019  |
| Qty.       | 2 m  |

## Accessories

### TS 35X7.5/LL 2M/ST/ZN

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Width      | 35 mm   | Width (inches)  | 1.378 inch |
| Height     | 35 mm   | Height (inches) | 1.378 inch |
| Depth      | 7.5 mm  | Depth (inches)  | 0.295 inch |
| Net weight | 312.5 g |                 |            |

### Material data

|          |        |                |                             |
|----------|--------|----------------|-----------------------------|
| Material | Steel  | Surface finish | galvanized, chromium-plated |
| Colour   | Silver |                |                             |

### System specifications

|         |           |               |                    |
|---------|-----------|---------------|--------------------|
| Version | with slot | Mounting rail | TS 35, TS 35 x 7.5 |
|---------|-----------|---------------|--------------------|

### Additional technical data

|                     |                 |                  |         |
|---------------------|-----------------|------------------|---------|
| Installation advice | Direct mounting | Type of mounting | Screwed |
|---------------------|-----------------|------------------|---------|

### Mounting rail

|                                 |        |   |                    |
|---------------------------------|--------|---|--------------------|
| Drill-hole diameter             | 5.2 mm | Short circuit strength corresponds to E-Cu wire | 16 mm <sup>2</sup> |
| Slit gap                        | 11 mm  | Slit length                                     | 25 mm              |
| Slit width                      | 5.2 mm | Slotted drill holes                             | Yes                |
| Solder eyelet hole diameter (D) | 5.2 mm | Spacing of holes, centre-to-centre              | 36 mm              |
| Thickness                       | 1 mm   |   |                    |

### Rating data

|           |              |
|-----------|--------------|
| Standards | DIN EN 60715 |
|-----------|--------------|

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001285    | ETIM 4.0   | EC001285    |
| ETIM 5.0   | EC001285    | ETIM 6.0   | EC001285    |
| UNSPSC     | 30-21-18-01 | eClass 5.1 | 27-14-06-04 |
| eClass 6.2 | 27-14-11-43 | eClass 7.1 | 27-14-11-43 |
| eClass 8.1 | 27-14-11-43 | eClass 9.0 | 27-14-11-43 |
| eClass 9.1 | 27-40-06-02 |            |             |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                    |  |
|--------------------|--|
| Brochure/Catalogue | <a href="#">CAT 1 TERM 16/17 EN</a>      |
| Engineering Data   | <a href="#">EPLAN, WSCAD, Zuken E3.S</a> |
| Engineering Data   | <a href="#">STEP</a>                     |

## Accessories

### TS 35X7.5/LL 2M/ST/ZN

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



### Building installation wiring

For building installations, we offer a complete system that revolves around the 10×3 copper rail and comprises perfectly coordinated components: from installation terminal blocks, neutral conductor terminal blocks and distribution terminal blocks to comprehensive accessories such as busbars and busbar holders.

### General ordering data

|            |  |
|------------|--|
| Type       | TS 35X7.5/LL 2M/ST/ZN  |
| Order No.  | <a href="#">051450000</a>  |
| Version    | Mounting rail, TS 35, TS 35 x 7.5, with slot, Steel, galvanized, chromium-plated |
| GTIN (EAN) | 4008190046019  |
| Qty.       | 2 m  |

## Accessories

### TS 35X7.5/LL 2M/ST/ZN

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Width      | 35 mm   | Width (inches)  | 1.378 inch |
| Height     | 35 mm   | Height (inches) | 1.378 inch |
| Depth      | 7.5 mm  | Depth (inches)  | 0.295 inch |
| Net weight | 312.5 g |                 |            |

### Material data

|          |        |                |                             |
|----------|--------|----------------|-----------------------------|
| Material | Steel  | Surface finish | galvanized, chromium-plated |
| Colour   | Silver |                |                             |

### System specifications

|         |           |               |                    |
|---------|-----------|---------------|--------------------|
| Version | with slot | Mounting rail | TS 35, TS 35 x 7.5 |
|---------|-----------|---------------|--------------------|

### Additional technical data

|                     |                 |                  |         |
|---------------------|-----------------|------------------|---------|
| Installation advice | Direct mounting | Type of mounting | Screwed |
|---------------------|-----------------|------------------|---------|

### Mounting rail

|                                 |        |   |                    |
|---------------------------------|--------|---|--------------------|
| Drill-hole diameter             | 5.2 mm | Short circuit strength corresponds to E-Cu wire | 16 mm <sup>2</sup> |
| Slit gap                        | 11 mm  | Slit length                                     | 25 mm              |
| Slit width                      | 5.2 mm | Slotted drill holes                             | Yes                |
| Solder eyelet hole diameter (D) | 5.2 mm | Spacing of holes, centre-to-centre              | 36 mm              |
| Thickness                       | 1 mm   |   |                    |

### Rating data

|           |              |
|-----------|--------------|
| Standards | DIN EN 60715 |
|-----------|--------------|

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001285    | ETIM 4.0   | EC001285    |
| ETIM 5.0   | EC001285    | ETIM 6.0   | EC001285    |
| UNSPSC     | 30-21-18-01 | eClass 5.1 | 27-14-06-04 |
| eClass 6.2 | 27-14-11-43 | eClass 7.1 | 27-14-11-43 |
| eClass 8.1 | 27-14-11-43 | eClass 9.0 | 27-14-11-43 |
| eClass 9.1 | 27-40-06-02 |            |             |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                    |  |
|--------------------|--|
| Brochure/Catalogue | <a href="#">CAT 1 TERM 16/17 EN</a>      |
| Engineering Data   | <a href="#">EPLAN, WSCAD, Zuken E3.S</a> |
| Engineering Data   | <a href="#">STEP</a>                     |