



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



10RC6F Ins Vinyl Fork Term 12-10 BLT NO6 Ye

Abb Installation Products, Inc

| | |
|------------------|--|
| Catalog Number | 10RC6F |
| Manufacturer | Abb Installation Products, Inc |
| Description | Vinyl-Insulated Fork Terminal, Length 1.09 Inches, Width .31 Inches, Maximum Insulation .210, Bolt Hole #6, Wire Range #12-#10 Awg, Color Yellow, Copper, Tin Plated |
| Weight per unit | 0.0100 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|----------------|-----------|
| Material | Copper |
| Voltage Rating | 600 V |
| Wire Size | 12-10 AWG |

Material, Color, and Finish

| | |
|-------|--------|
| Color | Yellow |
|-------|--------|

Descriptions

| | |
|------------------------|--|
| Description | INS VINL FORK TERM 12-10 BLT NO6 YE |
| extra long description | ABB 10RC-6F INS VINL FORK TERM 12-1 |
| Long Description | Vinyl-Insulated Fork Terminal, Length 1.09 Inches, Width .31 Inches, Maximum Insulation .210, Bolt Hole #6, Wire Range #12-#10 AWG, Color Yellow, Copper, Tin Plated |
| Product Type | Ins Vinyl Fork Term 12-10 BLT NO6 Ye |
| Special Features | These fork terminals have extra-long PVC insulation sleeve for protection and stress relief at wires flex point. Brazed seam barrel is serrated for high pull-out value. Insulation is color-coded |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Sta-Kon |
| GTIN | 00786210838199 |
| Manufacturers Part Number | 10RC-6F |
| UPC | 786210838199 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------------|
| Category Description | TERMINALS |
| Type | Vinyl Insulated Fork Terminal |

Packaging

| | |
|-----------------|------|
| Carton | 50 |
| Weight Per each | 0.01 |

Uses, Certifications, and Standards

| | |
|----------|---------------------|
| standard | UL E9809 / UL E9809 |
|----------|---------------------|