

Specifications

Photo is representative

Eaton OS10D7-W

Eaton occupancy sensor and dimmer, 8/10A, Resi/com, Flush, 120/277V, 6" pre-strip wrels, Pshpd w/hor dim/brite bar, White, 60 Hz, LED mot ind, 1-pole, 3-way, 0-40 °C, 1-ph, Poly, 1200/2200W, Used w/0-10 Vdc FLR/LED blst 748523

General specifications

PRODUCT NAME	Eaton occupancy sensor and dimmer
CATALOG NUMBER	OS10D7-W
UPC	032664748523
PRODUCT LENGTH/DEPTH	1.969 in
PRODUCT HEIGHT	4.252 in
PRODUCT WIDTH	2.756 in
PRODUCT WEIGHT	0.36 lb
CERTIFICATIONS	NOM cULus Listed
PRODUCT TYPE	Occupancy sensor and dimmer



Powering Business Worldwide

Product specifications

USED WITH	LED ballasts 0-10 Vdc FLR
FREQUENCY RATING	60 Hz
SPECIAL FEATURES	Dimmer sensor
TYPE	Occupancy sensor and dimmer
AMPERAGE RATING	8/10A
VOLTAGE RATING	120/277 V
NUMBER OF POLES	Single-pole
PHASE	Single-phase
POWER CONSUMPTION	1200 W 2200 W
CONFIGURATION	Horizontal dim/bright bar Push pad design
ILLUMINATION	LED motion indicator
APPLICATION	Residential, commercial
WIRING METHOD	6 inch pre-stripped wire leads
SENSOR TYPE	Occupancy
SWITCH TYPE	Single-pole, three-way
MOUNTING METHOD	Flush
CLOSURE TYPE	Maintained
MATERIAL	Polycarbonate
NUMBER OF WAYS	Three-way
OPERATING TEMPERATURE	0 to 40 °C
COLOR	White

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Resources

BROCHURES	Arrow Hart commercial lighting controls brochure
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - OS10D7-W 0-10V dimmer sensor spec sheet



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

