



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1001 Size 1 Antishort Bushing (14/4, 12/3, 6/1, 4/1) *Bridgeport Fittings*

| | |
|------------------|---|
| Catalog Number | 1001 |
| Manufacturer | Bridgeport Fittings |
| Description | Bushing, Anti-Short, Redheads, Polyethylene, Trade Size 1 |
| Weight per unit | 0.0009 (lbs/each) |
| Product Category | BX, MC, Armored Cable Fittings |

Features

| | |
|----------|---------|
| Material | Plastic |
| media | Yes |

Material, Color, and Finish

| | |
|--------|-----------|
| Color | Red |
| Finish | NO FINISH |

Dimensions and Weight

| | |
|------|---|
| Size | 1 |
|------|---|

Descriptions

| | |
|------------------------|---|
| Description | SIZE 1 ANTISHORT BUSHING (14/4, 12/3, 6/1, 4/1) |
| extra long description | BPT 1001 NO-1 ANTI-SHORT BUSHING |
| Long Description | Bushing, Anti-Short, Redheads, Polyethylene, Trade Size 1 |
| Product Type | No-1 Anti-Short Bushing |
| Special Features | 14/4, 12/3, 6/1, 4/1 |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Bridgeport |
| GTIN | 00781747010018 |
| Manufacturers Part Number | 1001 |
| UPC | 781747010018 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | COUPLINGS, ADAPTERS, REDUCERS, BUSHINGS, & CAPS |
| Type | BUSHING |

Trade Size

| | |
|------------|---|
| Trade Size | 1 |
|------------|---|

Availability

| | |
|-------------|----|
| minimum qty | 50 |
|-------------|----|

Packaging

| | |
|-----------------|--------|
| Carton | 50 |
| Package | 3500 |
| Weight Per each | 0.0009 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Polyethylene "Redheads" prevent damage to wire installation when placed between the wire and armored sheath. Rated 90 degree C.

standard

CSA, UL

Temperature Rating

90°C