



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 10250TM67 LGD PLT 1/2RND Man Auto Eaton Corp

Catalog Number	10250TM67
Manufacturer	Eaton Corp
Description	Eaton 10250T Pushbutton Legend Plate, 10250T Series, 1/2 Round Legend Plate, Black, Legend: Man. Auto, 5/32 In High, White Letters
Weight per unit	0.0100 (lbs/each)
Product Category	Legend Plates

### Features

dimensions	1.7000 IN X 1.6000 IN X 0.1000 IN
media	Yes

### Dimensions and Weight

Depth	1.6
Height	0.1
Size	1/2 round
Width	1.6

### Descriptions

Description	LGD PLT 1/2RND MAN AUTO
extra long description	ETN 10250TM67 LGD PLT 1/2RND MAN AU
Features	Eaton's 10250T line of 30.5 mm pushbuttons features a heavy-duty zinc die cast construction. Reliability nibs improve contact reliability even under dry circuit and fine dust conditions. In addition, drainage holes prevent the buildup of liquid inside the operator, which can prevent operation in freezing environments.
Long Description	Eaton 10250T pushbutton legend plate, 10250T series, 1/2 Round Legend Plate, Black, Legend: MAN. AUTO, 5/32 In high, White letters
Product Type	LGD PLT 1/2RND Man Auto
Special Features	Used with 10250T Series, Selector Switch and Roto-Push Operators

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113224527
Manufacturers Part Number	10250TM67
UPC	782113224527

### Taxonomies, Classifications, and Categories

Category Description	OILTIGHT OPERATORS.30MM
Type	Pushbutton accessory



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.01

## Uses, Certifications, and Standards

Application	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
standard	UL Listed, CSA Certified, CE Marked