



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

112 Pearl Street
67801-0000, KS Dodge City
Phone: 620-682-8503
Fax: 620-682-8504



14100AQD03 Ac/DC Ir Reflex With Micro Connector

Eaton Corp

Catalog Number	14100AQD03
Manufacturer	Eaton Corp
Description	Eaton Comet Series Tubular Photoelectric Sensor, Forward Viewing, Sensor Dist 25 FT., 300 Ma Max Ac L1 Switched/DC NPN Open Coll, 300 Ma Ac/DC At 20-264VAC/15-30VDC, 4 Pin Dual Key Micro Connector, Non Polarized Retroreflective, 8 In.(.2M)
Weight per unit	0.7000 (lbs/each)
Product Category	Photoelectric Sensors

Features

connection	4-pin dual key micro connector
------------	--------------------------------

Dimensions and Weight

Height	1.8
Length	0.47
Width	0.71

Descriptions

Description	AC/DC IR REFLEX WITH MICRO CONNECTOR
extra long description	ETN 14100AQD03 AC/DC IR REFLEX WITH
Features	Eaton's Comet Series Photoelectric Sensors is a complete line of high performance, 18 mm tubular sensors with a variety of models and modes to solve virtually any sensing problem.
Long Description	Eaton Comet Series Tubular Photoelectric Sensor, Forward Viewing, Sensor dist 25 Ft., 300 mA max AC L1 switched/DC NPN open coll, 300 mA AC/DC at 20-264Vac/15-30Vdc, 4 Pin Dual Key Micro Connector, Non Polarized Retroreflective, 8 in(.2m)
Product Type	Ac/DC Ir Reflex With Micro Connector

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113843667
Manufacturers Part Number	14100AQD03
UPC	782113843667

Taxonomies, Classifications, and Categories

Category Description	PROXIMITY SWITCHES AND CORDSETS
Type	Tubular photoelectric sensor

Packaging

Carton	1
Weight Per each	0.7



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

112 Pearl Street
67801-0000, KS Dodge City
Phone: 620-682-8503
Fax: 620-682-8504

Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & EOEM - Electrical Assemblies and
EOEMs - Other

Operating Temperature
standard

-40° to 158°F (-40° to 70°C)

cUL Recognized, UL Recognized, CE Marked