

Eaton 12100R6513

Catalog Number: 12100R6513

Eaton Comet 18mm tubular photoelectric sensor, Through Beam, 20 ft range, Right Angle, Output ON, 6.6 ft, 300 mA AC/DC at 20-264 Vac/15-30 Vdc, PVC, AC: L1 switched, DC: NPN open collector, 20-264 Vac 50/60 Hz, 15-30 Vdc (NPN)

General specifications



Product Name	Catalog Number
Eaton Comet 18mm tubular photoelectric sensor	12100R6513
	UPC
	782113821962
Product Length/Depth	Product Height
2.55 in	0.71 in
Product Width	Product Weight
0.47 in	0.7 lb
Warranty	Certifications
3 year	cUL Recognized
	UL Recognized

defaultTaxonomyAttributeLabel

Type

Photoelectric Sensor

Contact Rating

300 mA AC/DC at 20-264 Vac/15-30 Vdc

Cable type

Polyvinyl Chloride (PVC)

Enclosure material

Polyurethane foam (RIM)

Contact configuration

DC: NPN open collector

AC: L1 switched

Sensor type

Through beam

Input voltage

20-264 Vac at 50/60 Hz, 15-30 Vdc (NPN)

LED indicator

Output ON

Protection

Auto reset short circuit

Cord length

79.2 ft

Maximum AC current

300 mA

Maximum DC current

300 mA

Operating temperature - max

158 °F

Operating temperature - min

-4 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 4, NEMA 4X, NEMA 6, NEMA 12,
NEMA 13, IP69K

Resources

Brochures

[Comet series - Photoelectric sensors](#)

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

[Product Range Catalog Sensors – products, basic information, applications](#)

Specifications and datasheets

[Eaton Specification Sheet - 12100R6513](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)