



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 13104RQD03 R/A 2" Prox W/Conn Ac/DC *Eaton Corp*

|                  |   |
|------------------|---|
| Catalog Number   | 13104RQD03  |
| Manufacturer     | Eaton Corp  |
| Description      | Photoelectric Sensor, Rectangular Body Shape, Light Beam Sensing Method, 50 MM Sensing Distance, M12 X 1 Plug-In Connection, NPN Pole Throw Configuration, Polyurethane Material, 20 to 264 V Ac; 15 to 30 V DC, -40° to +158 °F, 0.67 LB |
| Weight per unit  | 0.6700 (lbs/each)   |
| Product Category | Photoelectric Sensors   |

### Features

|            |                                   |
|------------|-----------------------------------|
| connection | Dual key micro                    |
| dimensions | 3.0200 IN X 0.4700 IN X 0.7100 IN |

### Dimensions and Weight

|        |      |
|--------|------|
| Height | 0.71 |
| Length | 3.02 |
| Width  | 0.47 |

### Descriptions

|                        |                                     |
|------------------------|-------------------------------------|
| Description            | R/A 2" PROX W/CONN AC/DC            |
| extra long description | ETN 13104RQD03 R/A 2" PROX W/CONN A |

### Manufacturer Information

|       |                     |
|-------|---------------------|
| Brand | EATON CUTLER-HAMMER |
| GTIN  | 00782113968544      |
| UPC   | 782113968544        |

### Taxonomies, Classifications, and Categories

|                      |                                 |
|----------------------|---------------------------------|
| Category Description | PROXIMITY SWITCHES AND CORDSETS |
| Type                 | Tubular photoelectric sensor    |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 0.67 |

### Uses, Certifications, and Standards

|                       |   |
|-----------------------|---|
| Application           | Vehicles: On-Road - PickUp & Delivery: Food |
| Operating Temperature | -40° to 158°F (-40° to 70°C)                |
| standard              | cUL Recognized, UL Recognized               |