

# CABLE TIES

## UV & Weather Resistant (Black)

### Standard - Black Series



#### SPECIFICATIONS

- cULus Listed for Positioning Devices. UL62275.
- **Temperature Rating:** Min., -40°F to Max., 185°F (-40°C to 85°C)
- **Ideal Storage:** 23°C, Humidity 50%, Avoid storing cable ties next to warm objects.
- **Type 21 AH-2:** "Suitable for use in air-handling spaces (Plenums)".

#### FEATURES

- Made from weather resistant Nylon 66 for applications exposed to outside elements.
- UV resistant and Black color only.
- Made of high-strength Nylon 66 that resists abrasion and chemicals such as common oils, greases, solvents, dilute acids and alkalines.
- Fungus-resistant, self-extinguishing and have excellent dielectric properties.

CAT. NO.	MAX. WIRE/CABLE SIZE (L)	MAX BUNDLE DIAMETER	TENSILE STRENGTH	LENGTH (IN.)	WIDTH (IN.)	STD. PKG. QTY.	STD. CTN. QTY.
11400	11"	2.940	40 Lbs	11.100	0.189	100	2,000
11500	11"	3.125	50 Lbs	11.500	0.187	100	2,000
11500X	11"	3.125	50 Lbs	11.500	0.187	1000	2,000
11750	11"	3.000	75 Lbs	11.500	0.189	100	2,000
111200	11"	3.000	120 Lbs	11.500	0.300	100	2,000
14500	14"	4.070	50 Lbs	14.100	0.189	100	3,000
14500X	14"	4.070	50 Lbs	14.100	0.189	1000	3,000
14750	14"	4.070	75 Lbs	14.100	0.189	100	3,000
141200	14"	4.070	120 Lbs	14.250	0.300	100	2,000
152500	15"	4.375	250 Lbs	15.000	0.500	50	500
18500	18"	5.070	50 Lbs	18.000	0.189	100	2,000
181750	18"	5.250	175 Lbs	17.750	0.315	50	500
182500	18"	5.500	250 Lbs	18.870	0.500	50	500
222500	22"	6.875	250 Lbs.	22.87	0.500	50	500
241750	24"	7.140	175 Lbs	24.000	0.345	50	500
282500	28"	8.875	250 Lbs.	28.75	0.500	50	500
301750	30"	9.250	175 Lbs	30.000	0.354	50	500
342500	34"	10.5	250 Lbs.	34.68	0.500	50	500
361750	36"	11.000	175 Lbs	36.000	0.350	50	500
402500	40"	12.5	250 Lbs.	40.5	0.500	50	500
481750	48"	15.000	175 Lbs	48.000	0.354	50	500
601750	60"	18.250	175 Lbs	59.000	0.354	50	500

CABLE TIES