



## ***I. Product Description***

**CRC 2-26®** is a versatile, plastic safe, multi-purpose precision lubricant, penetrant and corrosion inhibitor. Its unique viscosity allows it to cover more surface area and penetrate deep into the surface of all metals, including steel, copper, brass and aluminum alloys. **2-26®** displaces moisture and leaves a thin, long lasting film to protect against corrosion.

## ***II. Applications***

Recommended for use on electrical connectors, relays, circuit breakers, transformers, switchgear, motors, generators, controls, instruments, communication assemblies, electronics, alarm systems, starters, tubing, castings, gears, weld rod, wire, fixtures, dies, jigs, shim stock, chucks, drill rod, heat treated parts, machined surfaces, finished welds, aluminum extrusions, air actuated tools, conveyors, frozen joints, locks, hoists, etc. Excellent for use around modern plastics and insulators. Recommended for restoring electrical properties to water or flood damaged equipment.

## ***III. Features & Benefits***

- **All-In-One Formula.** Fills the need for lubricant, penetrant, light duty cleaner and corrosion inhibitor in one product.
- **Displaces Moisture.** Prevents corrosion to improve equipment life and performance.
- **Plastic Safe.** Allows one product to be used in all applications without risk of costly damage to most sensitive modern plastics.
- **360° Valve.** Product can be sprayed from any position – even upside down.
- **M.S.D.[L.]™-Material Safety Data Label.** Provides instant access to current safety information should an accident or OSHA inspection occur. Helps comply with **OSHA Hazard Communications Standard 29 CFR 1910.1200.**

## ***IV. Physical Properties without propellant***

<b>Flash Point</b>	192°F / 89°C TCC	<b>Boiling Point (Initial)</b>	435°F / 224°C
<b>Odor</b>	Mild Petroleum	<b>Solubility</b>	Neg. in water
<b>Appearance</b>	Amber liquid	<b>VOC %</b>	0
<b>Vapor Density</b>	>air	<b>Specific Gravity</b>	0.82
<b>VOC Content (Fed)</b>	0 g/L	<b>Temperature Range</b>	Max 250°F
<b>Sara Title III, Sect. 313 Chemicals</b>	No	<b>Propellant</b>	CO <sub>2</sub>
<b>Prop 65</b>	No		

## ***V. Specifications and Approvals***

- NSF H2 Registered for use in meat and poultry plants.
- NSN# 6850-00-874-5847.

## VI. Performance Characteristics

Type of Film	Non-drying
Film Thickness	0.025 to 0.075 mils
Bellcore Test (Plastic Compatibility)	Passed
ASTM D-877 (Dielectric Strength)	51,300 volts
ASTM D-56 (Flash Point)	192°F (TCC)
ASTM D-3233 (Falex Load Test)	1,500 lbs.
Corrosion Inhibitor	Indoor Only/up to 9 months Ferrous and Non-Ferrous Metals

## VII. Directions

- Spray light even coat to protect surfaces and to seal out moisture.
- Apply liberally to loosen rusted parts.
- Spray wet surfaces until run-off is clear and moisture free.
- **For personal safety do not use on energized equipment.** Allow to dry at least 4 to 6 hours before energizing.
- Contact CRC Technical Service for directions for restoring electrical properties to water or flood damaged equipment.

## VIII. Package Description

Part Number	Container Size
02004	6 oz Aerosol
02005	16 oz Aerosol
02006	1 Gallon Bottle
02007	16 oz Spray Bottle
02009	5 Gallon Pail
02011	55 Gallon Drum
02024	2 oz Aerosol

## IX. Disposal

Disposal requirements vary by state and local jurisdiction. All used and unused product should be disposed of in conformance with local, state and federal regulations.

## X. Special Use Warnings

### Aerosol Cans

Do not puncture, incinerate or store above 120°F. Exposure to high temperatures may cause can to burst. Do not place in direct sunlight or near any heat source. Aerosol cans will conduct electricity. Keep away from all live electrical sources including battery terminals, solenoids, electrical panels and other electronic components. Failure to observe this warning may result in serious injury from flash fire and/or electrical shock.

### General

Use only in well ventilated area. Ventilation may be improved by opening a window or door or providing mechanical assistance. Avoid continuous breathing of vapor and spray mist. Avoid contact with skin and eyes. If ventilation is not adequate, respiratory protection should be worn. For more information regarding short term and long term exposure, review this product's Material Safety Data Sheet.

**DISCLAIMER:** This information is accurate to the best of CRC Industries' knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. All products should be tested for suitability on a particular application prior to actual use. CRC Industries, Inc. makes no representations or warranties of any kind concerning this data.

CRC Industries, Inc.  
Technical Service: (800)521-3168

Industrial Products Division  
Customer Service: (800)272-4620

Warminster, PA 18974  
CRC On-Line: (215)442-6260



## I. Product Description

**CRC 2-26®** is a versatile, plastic safe, multi-purpose precision lubricant, penetrant and corrosion inhibitor. Its unique viscosity allows it to cover more surface area and penetrate deep into the surface of all metals, including steel, copper, brass and aluminum alloys. **2-26®** displaces moisture and leaves a thin, long lasting film to protect against corrosion.

## II. Applications

Recommended for use on electrical connectors, relays, circuit breakers, transformers, switchgear, motors, generators, controls, instruments, communication assemblies, electronics, alarm systems, starters, tubing, castings, gears, weld rod, wire, fixtures, dies, jigs, shim stock, chucks, drill rod, heat treated parts, machined surfaces, finished welds, aluminum extrusions, air actuated tools, conveyors, frozen joints, locks, hoists, etc. Excellent for use around modern plastics and insulators. Recommended for restoring electrical properties to water or flood damaged equipment.

## III. Features & Benefits

- **All-In-One Formula.** Fills the need for lubricant, penetrant, light duty cleaner and corrosion inhibitor in one product.
- **Displaces Moisture.** Prevents corrosion to improve equipment life and performance.
- **Plastic Safe.** Allows one product to be used in all applications without risk of costly damage to most sensitive modern plastics.
- **360° Valve.** Product can be sprayed from any position – even upside down.
- **M.S.D.[L.]™-Material Safety Data Label.** Provides instant access to current safety information should an accident or OSHA inspection occur. Helps comply with **OSHA Hazard Communications Standard 29 CFR 1910.1200.**

## IV. Physical Properties without propellant

Flash Point	192°F / 89°C TCC	Boiling Point (Initial)	435°F / 224°C
Odor	Mild Petroleum	Solubility	Neg. in water
Appearance	Amber liquid	VOC %	0
Vapor Density	>air	Specific Gravity	0.82
VOC Content (Fed)	0 g/L	Temperature Range	Max 250°F
Sara Title III, Sect. 313 Chemicals	No	Propellant	CO <sub>2</sub>
Prop 65	No		

## V. Specifications and Approvals

- NSF H2 Registered for use in meat and poultry plants.
- NSN# 6850-00-874-5847.

## VI. Performance Characteristics

Type of Film	Non-drying
Film Thickness	0.025 to 0.075 mils
Bellcore Test (Plastic Compatibility)	Passed
ASTM D-877 (Dielectric Strength)	51,300 volts
ASTM D-56 (Flash Point)	192°F (TCC)
ASTM D-3233 (Falex Load Test)	1,500 lbs.
Corrosion Inhibitor	Indoor Only/up to 9 months Ferrous and Non-Ferrous Metals

## VII. Directions

- Spray light even coat to protect surfaces and to seal out moisture.
- Apply liberally to loosen rusted parts.
- Spray wet surfaces until run-off is clear and moisture free.
- **For personal safety do not use on energized equipment.** Allow to dry at least 4 to 6 hours before energizing.
- Contact CRC Technical Service for directions for restoring electrical properties to water or flood damaged equipment.

## VIII. Package Description

Part Number	Container Size
02004	6 oz Aerosol
02005	16 oz Aerosol
02006	1 Gallon Bottle
02007	16 oz Spray Bottle
02009	5 Gallon Pail
02011	55 Gallon Drum
02024	2 oz Aerosol

## IX. Disposal

Disposal requirements vary by state and local jurisdiction. All used and unused product should be disposed of in conformance with local, state and federal regulations.

## X. Special Use Warnings

### Aerosol Cans

Do not puncture, incinerate or store above 120°F. Exposure to high temperatures may cause can to burst. Do not place in direct sunlight or near any heat source. Aerosol cans will conduct electricity. Keep away from all live electrical sources including battery terminals, solenoids, electrical panels and other electronic components. Failure to observe this warning may result in serious injury from flash fire and/or electrical shock.

### General

Use only in well ventilated area. Ventilation may be improved by opening a window or door or providing mechanical assistance. Avoid continuous breathing of vapor and spray mist. Avoid contact with skin and eyes. If ventilation is not adequate, respiratory protection should be worn. For more information regarding short term and long term exposure, review this product's Material Safety Data Sheet.

**DISCLAIMER:** This information is accurate to the best of CRC Industries' knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. All products should be tested for suitability on a particular application prior to actual use. CRC Industries, Inc. makes no representations or warranties of any kind concerning this data.

CRC Industries, Inc.  
Technical Service: (800)521-3168

Industrial Products Division  
Customer Service: (800)272-4620

Warminster, PA 18974  
CRC On-Line: (215)442-6260