

# 2110 SERIES

## 1/2" CONDUIT MOUNTING DIE CAST ALUMINUM PHOTOCONTROL



### APPLICATIONS

- Parking lot lighting
- Building perimeter lighting
- Outdoor signage



### FEATURES

**SENSOR:** Conformal coated cadmium sulphide photocell resists effects of moisture and airborne contaminants. Photocell responds to the light spectrum near to that of a human eye.

**STANDARDS:** Meets ANSI/UL773A.

**OPERATION:** Delay of up to two minutes to prevent false switching due to light from passing vehicles, lightning, etc.

**HOUSING:** Die cast aluminum housing and base. Gasketed for weather protection.

**ENERGY SAVINGS:** Works with screw base CFLs.

### SPECIFICATIONS

**ON/OFF:** Turn ON is 1 to 5fc, Turn OFF is 3 to 15fc, without the slide in position. ON/OFF adjustment is easily made by moving a slide cover. No tools required.

**TIME DELAY:** ON and OFF.

**CELL:** Cadmium sulphide, epoxy conformal coated 1/2" diameter. MODEL 2117 is 1" cell.

**CONTACTS:** Remain closed between dusk and dawn (the unit fails in the ON position).

**LEAD WIRES:** Three color coded, minimum 6" wire leads, #16AWG, rated for 105 °C. (2117 #10AWG red and black).

**POWER CONSUMPTION:** Averages under 1 watt.

**TEMPERATURE RANGE:** -40 °F to +140 °F (-40 °C to +60 °C).

**FAIL MODE:** ON.

**WARRANTY:** 5 years.

CAT. NO.	UPC CODE	VOLTAGE (VAC) 50-60Hz	RATING		LED
			TUNGSTEN	BALLAST	
2115	60032	120	2000W	1800VA	600VA
2116	60033	208-277	3470-4620W	2080-2770VA	1040-1385VA
2117*	60037	120	3000W	3000VA	-
73866	62020	Mounting Bracket	-	-	-

\*Not UL or CSA rated.

