

# LED CORDLIGHT

Engineered Products Company's (EPCO) LED CordLights are an energy efficient, labor saving alternative to traditional string lights. Constructed of heavy-duty 18/2 SJTW round cord and available in 50- or 100-foot lengths, these CordLights are ETL Listed, comply with UL Standard 153 for Portable Electric Luminaires, and are suitable for a variety of temporary construction lighting applications.

## BENEFITS

- Each LED Module produces excellent 5000K white light.
- Labor savings! Easy installation and no lamps to replace.
- Reduced energy costs with minimal power draw.
- Tested for optimal performance, durability, and reliability.
- Suitable for damp and wet locations.
- IP65 Weather-resistant LED Modules resist dust and rain.
- Beam Angle: 120°.
- Linkable to connect additional LED CordLights up to 500-feet.

## FEATURES

- Commercial grade, high-power LEDs.
- Available in 50- or 100-foot lengths.
- 10-foot spacing between LED Modules.
- Constructed of heavy-duty 18/2 SJTW round cord.
- 120-Volt plug and receptacle.
- Includes carabiner coupling link to expedite installation.

## TYPICAL APPLICATIONS

- |                               |                            |
|-------------------------------|----------------------------|
| ▪ Construction Sites          | ▪ Special Events           |
| ▪ Parking Lots                | ▪ Christmas Tree Lots      |
| ▪ Walkways                    | ▪ Outdoor Markets          |
| ▪ Bar and Restaurant Lighting | ▪ Commercial               |
| ▪ Festivals                   | ▪ Patio and Outdoor Spaces |
| ▪ Circus Tents                | ▪ Home Décor Lighting      |



LED CORDLIGHT



Carabiner Coupling Link



120-Volt Plug and Receptacle

# LED CORDLIGHTS

LED CORDLIGHTS SPECIFICATIONS		
	16040 — 100-Foot Length	16045 — 50-Foot Length
Output Lumens	10,000 (1,000 per LED Light Module)	5,000 (1,000 per LED Light Module)
Operating Voltage	120 VAC @ 60/50 Hz	120 VAC @ 60/50 Hz
Power Consumption	80-Watts	40-Watts
Correlated Color Temperature (CCT)	5000K	5000K
Color Rendering Index (CRI)	≥80	≥80
Efficacy	125 lm/W	125 lm/W
Ambient Operating Temperature	-4°F (-20°C) to 104°F (40°C)	-4°F (-20°C) to 104°F (40°C)
Environment	Damp or Wet Locations	Damp or Wet Locations
Certifications	<ul style="list-style-type: none"> <li>Complies with UL Standard 153 for Portable Electric Luminaires</li> <li>ETL Listed. Product Compliant to North American Safety Standards</li> <li>Meets all OSHA Standards</li> <li>Meets the requirements of the 2020 National Electrical Code</li> </ul>	<ul style="list-style-type: none"> <li>Complies with UL Standard 153 for Portable Electric Luminaires</li> <li>ETL Listed. Product Compliant to North American Safety Standards</li> <li>Meets all OSHA Standards</li> <li>Meets the requirements of the 2020 National Electrical Code</li> </ul>
Power Cord Type	<ul style="list-style-type: none"> <li>18/2 Heavy Duty SJTW Cord</li> <li>120V Plug and Receptacle</li> </ul>	<ul style="list-style-type: none"> <li>18/2 Heavy Duty SJTW Cord</li> <li>120V Plug and Receptacle</li> </ul>
LED Module/Power Cord Color	Black/Yellow	Black/Yellow
Warranty	1 Year	1 Year
Linkable Maximum	Five (5) Maximum	Ten (10) Maximum

## Replacement Fuse: Bussman Series — Product Code: GMA8-R

Catalog Number	UPC Number	Description	Order Unit	Unit Qty	Unit Pkg	Units/Case	TL Case Qty	Min Order Qty	MM Req	Ship Wt (Lbs)
16040	16040	LED CordLights: 100-FT Length	EA	1	BX	2	2	1	No	20
16045	16045	LED CordLights: 50-FT Length	EA	1	BX	4	4	1	No	20

## Distributed By:



### UNITS OF MEASURE KEY

Order Unit: The Unit to be ordered; Order Qty: Number of pieces in each Unit; Unit Pkg: Packaging types - BG (Bag), BX (Box), BRL (Barrel); Units/Case: Unit packages contained in the Case; TL Case Qty: The total number of items in each Master Case; Min Order Qty: The smallest Unit that can be ordered; MM Req: Must order multiples of the Unit in the stated quantities; Ship Wt (Lbs): Total weight of the units per Carton

E02-150-042 A1 (10/19-BB)  
©2019 Engineered Products Company. All Rights Reserved.

[www.engproducts.com](http://www.engproducts.com)

5401 SMETANA DRIVE | MINNETONKA, MN 55343  
P 800.336.1976 | F 800.336.2801

Specifications subject to change without prior notice.



**ENGINEERED  
PRODUCTS CO.**