Specifications



Photo is representative

Eaton 170M6760

Fuse-link, high speed, 630 A, AC 690 V, size 3, 76 x 92 x 139 mm, aR, IEC, UL, single indicator

General specifications	
PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M6760
UPC	051712792752
EAN	5996516020661
PRODUCT LENGTH/DEPTH	168 mm
PRODUCT HEIGHT	76 mm
PRODUCT WIDTH	95 mm
PRODUCT WEIGHT	959 g
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized



		oeci		

TYPE Fuse

esn	ш	•

APPLICATION	semiconductor protection
AMPERAGE RATING	630 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Centre fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	3
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	114 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	Other
CLASS	Class aR
CLEARING (I2T)	210000 at 660 V
WATT LOSSES	105 W
FUSE SHAPE	Square body, center bolted tags
PRE ARC (I2T)	31000
COLOR	None
INTERRUPT RATING	200 kAIC
FITTED WITH:	Type K Indicator for micro
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	3
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V
FUSE TYPE	US Style FKE/115 Type K indicator for micro Bolted tag
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

	eaton-bussmann-series-iec- high-speed-fuses-catalogue- ca135001en-en-gb.pdf
CATALOGS	Bussmann series complete full line catalog no. 1007
	170M6760~Eaton Bussmann series high speed square body fuse

PROJECT NAME:	
PROJECT NUMBER:	

PREPARED BY:	
DATE:	



Eaton Corporation plc

Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.







