

RTC

Recessed LED center basket

Metalux



RTC Recessed LED center basket

The RTC lensed troffer series provides performance, reliability and flexibility with a housing optimized for shallow plenums. Developed with Cooper Lighting Solutions' latest generation of solid-state components and electronic driver technologies, these center illuminated troffers provide numerous options for color, lumens, controls and sensing. Designed to be compatible with popular ceiling systems, the RTC troffers are ideal for both new construction and remodel/ replacement of fluorescent troffers in commercial office spaces, schools, healthcare facilities, and retail merchandising areas.


Low profile perfect for renovation or new construction

Contractor friendly, quick and easy install

No maintenance required


Center basket appeal, prismatic troffer value

Buy with confidence - proven Metalux quality




Durable construction

- Uniform body, strong cold rolled steel
- Impact-resistant polycarbonate lens
- Fast install with easy wiring access and plug-in wire connectors
- T-grid clips included
- Standard access plate with trade-size knockouts and large wiring compartment



Architectural appeal


- Advanced optical control with linear prisms for uniform light distribution
- Matte white post-fabrication painted from corner to corner
- Selective binning to ensure color consistency
- 83 CRI with 3500K and 4000K



Features and benefits



- 2-3/8" [60mm]
- Low profile
- Perfect for shallow/restricted plenums



- Lutron and DALI options with UL 924 Emergency options
- Flexibility to meet building codes and safety requirements

Accessories



- Grid Retention
- Optional EQ clip (RTCEQ)
- Code and specification



- Integrated sensors factory wired and tested
- Simplicity - The lighting plan is the controls plan
- WaveLinx Wireless Connected Lighting System
- Enlighted Wireless Connected Lighting System

Connected Lighting Systems

WaveLinx Wireless Connected Lighting System



- Adjustable occupancy sensing and daylight dimming control
- Simple, secure wireless connectivity with out-of-the-box code compliance
- Easy to use mobile application allows for fast set up and unlocks advanced control capabilities
- Detection pattern covers standard ceiling applications up to 12 feet

Enlighted Wireless Connected Lighting System



- Configurable dimming, occupancy, light, temperature and power use sensing
- Enterprise-class wireless networking with fully addressable settings
- Powerful software for energy management and Internet of Things (IoT) data capture and analytics
- Low bay detection pattern covers low- and high-ceiling applications up to 20 feet



Performance

High lumen options enable use in high ceilings
True replacement two and three lamp troffers with T8, T5 or Biax lamps
Up to 60% energy savings
System lasts over 25 years with TM21 rating of L75, 60,000 hours
Five year warranty

Energy data¹

RTC				Popular fluorescent fixtures			Energy savings
Catalog No. (4000K) ³	Lumens ²	Watts	Efficiency lm/W	Fixture type	Lumens*	Wattage	
24RTC4840	4922	37.8	130	Parabolic 332	5646	83.0	54%
				Troffer 232	4400	55.4	32%
				Indirect Basket 332	4583	83.7	55%
24RTC6840	7195	57.1	126	Troffer 332	6629	81.7	30%
				Troffer 432	8402	109.7	48%
22RTC3440	3632	28.6	127	Indirect Basket 2BX40	4324	68.2	58%
				Troffer 2U6T8	3862	52.1	45%
22RTC4840	4889	38.1	128	Indirect Basket 332	4583	83.7	54%
				Indirect Basket 2BX40	4324	68.2	44%
				Troffer 2U6T8	3862	52.1	27%
				Direct Dual Lens 224	2975	52.0	27%
14RTC3440	3643	28.6	127	Parabolic 2U6T8	2791	58.8	35%
				Troffer 232	4224	55.4	48%

¹ Additional lumen options available see spec sheet for details.

² Lumens listed are delivered lumens.

³ Also available in 3500K.

Compliance and approvals



Lighting Product Lines

Ametrix
AtLite
Corelite
Ephesus
Fail-Safe
Halo
Halo Commercial
Invue
io
Iris
Lumark
Lumière
McGraw-Edison
Metalux
MWS
Neo-Ray
Portfolio
RSA
Shaper
Streetworks
Sure-Lites

Controls Product Lines

Fifth Light Technology
Greengate
iLight (International Only)
iLumin
Zero 88

Connected Lighting Systems

Distributed Low-Voltage Power
HALO Home
iLumin Plus
Enlighted
WaveLinx
Trellix



Cooper Lighting Solutions
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.cooperlighting.com

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2020 Cooper Lighting Solutions
All Rights Reserved
Printed in USA
Publication No. BR519032EN
September 9, 2020 12:10 PM

Cooper Lighting Solutions is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.