



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3705 Lee Street  
71302-0000, LA Alexandria  
Phone: 318-445-1336  
Fax: 318-445-8356



## 20AC1L 20A 120/277VAC B+S Wire SP Lock SW Gy

*Pass & Seymour/Legrand*

Catalog Number	20AC1L
Manufacturer	Pass & Seymour/Legrand
Description	1-Pole Lock Switch, Back and Side-Wire, 20A 120/277V
Weight per unit	0.1900 (lbs/each)
Product Category	Gen Purpose Switches

### Features

action	Single pole
actuator	Toggle Switch
amperage rating	20
Contact Rating	20 Amp, 120/277 VAC
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	CFL, Universal, LED, Fluorescent, Incandescent, Halogen, Xenon
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	1
Switch Type	Toggle
throw type	Single Throw
Voltage	120/277 V
Voltage Rating	120/277
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	3.3 in
------	--------

### Descriptions

Description	20A 120/277VAC B+S WIRE SP LOCK SW GY
extra long description	P&S PS20AC1L 20A 120/277VAC B+S WIR
Features	Chemical Resistant
Long Description	1-Pole Lock Switch, Back and Side-Wire, 20A 120/277V
Product Type	20A 120/277VAC B+S Wire SP Lock SW Gry
Special Features	Back & side wire, locking support, heavy duty toggle



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3705 Lee Street  
71302-0000, LA Alexandria  
Phone: 318-445-1336  
Fax: 318-445-8356

## Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007195613
Manufacturers Part Number	PS20AC1L
UPC	785007195613

## Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	SWITCH

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	10
Weight Per each	0.19

## Uses, Certifications, and Standards

Application	Industrial Spec Grade
Enclosure	Nylon
Mounting standard	WALL FEDSPEC, CULUS, UL 498/20, FEDSPEC