Decorator Screwless, Mid-Size and Standard

Contemporary design, sleek elegant lines, and a multitude of material, size and color choices make the Decorator Style an easy choice.



Gang	Description	Cat. No.	Color				
Mid-Siz	9						
1-Gang	Screwless	PJS26	A, B, BK, GY, LA, V, W				
2-Gang	Screwless	□ PJS262	A, B, BK, GY, LA, V, W				
3-Gang	Screwless	□ PJS263	A, BK, LA, V, W				
4-Gang	Screwless	□ PJS264	A, BK, LA, V, W				
5-Gang	Screwless	□ PJS265	A, BK, LA, V, W				
6-Gang	Screwless	□ PJS266	A, BK, LA, V, W				
1.0000	Delveerbenete	□ PJ26	A, B, BK, BL, GY, LA, RD, V, W				
1-Gang	Polycarbonate	□ PJ262					
2-Gang	Polycarbonate		A, B, BK, BL, GY, LA, RN, RD, V, W				
3-Gang	Polycarbonate	□ PJ263	A, B, BK, GY, LA, V, W				
4-Gang	Polycarbonate	□ PJ264	A, B, BK, GY, LA, V, W				
5-Gang	Polycarbonate	□ PJ265	A, B, BK, GY, LA, V, W				
6-Gang	Polycarbonate	□ PJ266	A, B, BK, GY, LA, V, W				
1-Gang	Thermoset	□ 2051	A, B, LA, V, W				
2-Gang	Thermoset	□ 2052	A, LA, V, W				
3-Gang	Thermoset	□ 2063	A, LA, V, W				
4-Gang	Thermoset	□ 2064	A, LA, V, W				
1-Gang	Stainless Steel	□ 93934	SS				
2-Gang	Stainless Steel	□ 93935	SS				
3-Gang	Stainless Steel	□ 93936	SS				
Standar	d-Size						
1-Gang	Nylon	□ 5151	A, B, BK, BL, GY, LA, RD, V, W				
2-Gang	Nylon	□ 5152	A, B, BK, GY, LA, V, W				
1-Gang	Thermoset	□ 2151	A, B, BK, GY, LA, V, W				
2-Gang	Thermoset	□ 2152	A, B, BK, GY, LA, V, W				
3-Gang	Thermoset	□ 2163	A, B, GY, LA, V, W				
4-Gang	Thermoset	□ 2164	A, B, LA, V, W				
5-Gang	Thermoset	□ 2165	A, B, LA, V, W				
6-Gang	Thermoset	□ 2166	A, B, LA, V, W				
0-Gang	mernoset		A, D, LA, V, W				
1-Gang	Stainless Steel	□ 93401	SS				
2-Gang	Stainless Steel	□ 93402	SS				
3-Gang	Stainless Steel	□ 93403	SS				
4-Gang	Stainless Steel	□ 93404	SS				
5-Gang	Stainless Steel	□ 93405	SS				
6-Gang	Stainless Steel	□ 93406	SS				
1-Gang	Brass	□ 94401	Brass				
2-Gang	Brass	□ 94401	Brass				
	For ordering wallplates, include Cat. No. followed by the color code: A (Almond)						

For ordering wallplates, include Cat. No. followed by the color code: A (Almond), B (Brown), BK (Black), BL (Blue), GY (Gray), LA (Light Almond), RD (Red), RN (Orange), SS (Stainless Steel), V (Ivory), W (White)

Regulatory

1.31" (33.3mm)

- UL 514D and cUL Listed, UL file #E33216
- Meets Federal Specification WP-455. Meets all CSA requirements, C22.2 no. 42.1
- Meets flammability requirements per UL 94, V2 rated
- Screwless wallplates appear to float freely on the surface of the wall

Screwless

- Mounting plate attaches to the wiring device and the wallplate is simply pressed into place for an easy and fast installation.
- Mid-sized to cover wall imperfections and large wallboard openings
- Virtually unbreakable polycarbonate construction

www.CoreLightingControls.com

Thermoplastic

- Exclusive time-saving Screw-Catch[™] feature holds mounting screws captive, simplifying installation
- Nylon wallplates are flush-fitting and warp resistant
- Polycarbonate wallplates are virtually unbreakable, with high structural rigidity, longterm form retention, and superior impact resistance
- Temperature rating: -40°C to 70°C

Mounting Holes for Wallplates and Covers

These are the most common nominal spacings for mounting holes on wallplates and covers. Holes are normally countersunk for oval head #6-32 screws.





Plate and Cover Opening Dimensions

Cover Openings

Nominal dimensions for plate and cover openings conform to industry standards and practices.





3-Wire Power

Device



Single Locking

Receptacle


20/30 AMP



Single Receptacle


Common Opening Configurations

Device







Description		Height	Width	First Gang to Edge	Gang to Gang
1-Gang	Standard	4.50" (114.3mm)	2.75" (69.8mm)	1.37" (34.9mm)	_
	Mid-Size	4.87" (123.8mm)	3.12" (79.4mm)	1.56" (39.7mm)	_
	Oversize	5.25" (133.3mm)	3.50" (88.9mm)	1.75" (44.4mm)	_
2-Gang	Standard	4.50" (114.3mm)	4.56" (115.9mm)	1.37" (34.9mm)	1.81" (46.0mm)
	Mid-Size	4.87" (123.8mm)	4.94" (125.4mm)	1.56" (39.7mm)	1.81" (46.0mm)
	Oversize	5.25" (133.3mm)	5.31" (134.9mm)	1.75" (44.4mm)	1.81" (46.0mm)
3-Gang	Standard	4.50" (114.3mm)	6.37" (161.9mm)	1.37" (34.9mm)	1.81" (46.0mm)
	Mid-Size	4.87" (123.8mm)	6.75" (171.4mm)	1.56" (39.7mm)	1.81" (46.0mm)
	Oversize	5.25" (133.4mm)	7.17" (182.2mm)	1.75" (44.4mm)	1.81" (46.1mm)
4-Gang	Standard	4.50" (114.3mm)	8.19" (207.9mm)	1.37" (34.9mm)	1.81" (46.0mm)
	Mid-Size	4.87" (123.8mm)	8.56" (217.5mm)	1.56" (39.7mm)	1.81" (46.0mm)
	Oversize	5.25" (133.3mm)	8.94" (227.0mm)	1.75" (44.4mm)	1.81" (46.0mm)
5-Gang	Standard	4.50" (114.3mm)	10.00" (254.0mm)	1.37" (34.9mm)	1.81" (46.0mm)
	Mid-Size	4.87" (123.8mm)	10.37" (263.5mm)	1.56" (39.7mm)	1.81" (46.0mm)
6-Gang	Standard	4.50" (114.3mm)	11.81" (300.0mm)	1.37" (34.9mm)	1.81" (46.0mm)
	Mid-Size	4.87" (123.8mm)	12.18" (309.5mm)	1.56" (39.7mm)	1.81" (46.0mm)







Standard





Specification Grade Ground Fault Circuit Interrupter Receptacles

Back Wire &

Side Wire

Description

Auto Ground Duplex GFCI

Duplex GFCI

Tamper Resistant

Specification Grade Automatic Ground GFCIs

2-Pole, 3-Wire Grounding 15A, 125V/AC 20A, 125V/AC NEMA 5-15, 5-20



-AG

c(VL)us NOM

20A. 125V

Catalog No.

V. W

NEMA 5-20R

Color Suffix

□ VGF20__-AG


BK, V, W

	1.30" (33.0mm)	
1	030	
	11	0
4.19" (106.4mm)	I.L	
(83.3mm)	11	0
ļ	0.0	1.20" (30.5mm)

VGF15-AG



VGFS15-MSP



VGFD20

	Specification	Grade Combination	GFCI Receptacle & Switch
- 1			

15A. 125V

NEMA 5-15R

Catalog No.

BK, V, W

15A, 125V

NEMA 5-15R Catalog No.

Color Suffix

V, W

□ VGFS15 -MSP

V, W

Color Suffix

UVGF15___-AG

TRVGF15___-AG

Back Wire & Side Wire	
Description	
NEMA 5-15 GFCI Receptacle with Feed-Through Single-Pole Switch (rated 1800W @ 120V/AC, 60Hz)	

Includes standard size unbreakable wallplate

Includes mid-size unbreakable wallplate

Specification	Grade Bla	nk Face	GECI


Back Wire & Side Wire	20A, 125V c(h) us 10M
Description	Catalog No. Color Suffix
Blank Face (Dead Front) GFCI, Rated as 1.5HP Motor Control Switch	□ VGFD20 V, W
Includes standard size unbreakable wallplate	

Color Ordering Information

For ordering devices, include Cat. No. followed by the color code: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), RD (Red), RN (Orange), V (Ivory), W (White)

Icon Key

NAFTA Compliant - see page O-30



Accessories for GFCIs		
Description	Catalog No.	4
GFCI 7/8" extension ring Add color suffix: B (Brown), BLK (Black), LA (Light Almond), V (Ivory), W (White))	GFER	_
Metal self-closing horizontal 1-gang weather protective cover, decorator opening	□ S1966	٠
While-In-Use metal weather protective standard depth 1-gang cover, vertical mount	UWUMV-1	٠

Specification Information:

Specification Grade GFCI: G-13 Specification Grade Combo GFCI Receptacle & Switch: G-14 Specification Grade Blank Face GFCI : G-14







www.arrowhart.com

.

COOPER Wiring Devices

Wallplates

Standard Size Mid-Size Oversize REPEL

	Wallplate Type	Standard Size, Mid-Sized & Oversize Wallplates				REPEL	
	Material Type	Thermoset	Nylon	Stainless Steel	Polycarbonate	REPEL Polycarbonate Mid-Sized Wallplates PJ_AM and PJS_AM Series	REPEL Stainless Steel Standard Size Wallplates 93070_AM, 93090_AM, 93100_AM, 93400_AM Series
	Manufacturing Process	Injection Molded	Injection Molded	Stamped	Injection Molded	Injection Molded	Stamped
		UL Listed to UL 514D, file no. E33216	UL Listed to UL 514D, file no. E33216	UL Listed to 514D, file no. E92003	UL Listed to UL 514D, file no. E33216	UL Listed to UL 514D, file no. E33216	UL Listed to UL 514D, file no. E92003
	Testing & Code Compliance	et contraction of the second s	cUL certified to C22.2, no. 42.1,	CSA certified to C22.2, no. 42.1	cUL, UL file E33216 certified	Agion [®] Antimicrobial Additive: EPA approved for use as product ingredient	Agion [®] Antimicrobial Additive: EPA approved for use as product ingredient
		UL file E33216	UL file E33216		to C22.2, no. 42.1	PJ_AM only: cUL Listed to CSA C22.2, no 42.1, file no. E33216	CSA certified to C22.2, no. 42.1
Specifications: Environmental	Flammability	Meets UL 94 requirements; 5V rated	Meets UL 94 requirements; 5V rated	N/A	Meets UL 94 requirements 5VA rated	Meets UL 94 requirements; 5V rated	N/A
Specific Environ	Temperature Rating	-40°C to 90°C (-40°F to 194°F)	-40°C to 70°C (-40°F to 158°F)	-40°C to 70°C (-40°F to 158°F)	-40° to 70° C (-40°F to 158°F)	-40°C to 70°C (-40°F to 158°F)	-40°C to 70°C (-40°F to 158°F)
Materials:	Rody	0.080" thick thermoset urea or phenolic	0.060" thick thermoplastic	0.032" thick stainless steel alloy, 18% chromium and 8% nickel for corrosion resistance	0.08" thick thermoplastic polycarbonate	0.071" thick polycarbonate with Agion® Antimicrobial Additive incorporated	0.032" thick 302/304 stainless steel alloy, 18% chromium and 8% nickel for corrosion resistance, DuPont® Alesta® powder coating with Agion® Antimicrobial incorporated
	Inner Wallplate	N/A	N/A	N/A	0.071" thick polycarbonate	PJS_AM only: 0.071" thick polycarbonate	N/A

NOTE: REPEL products do not protect the user against disease causing organisms and ongoing regular cleaning practices should be maintained. Agion is a registered trademark of Agion Technologies, Inc., Wakefield, MA