



**Smooth style and operation —
plus commercial durability.**

2601, 2603, 2604, 2621, 2622, 2623, 2624

Cushioned thermoplastic paddles assure smooth, quiet long-term use. Integral silver-alloy contacts combine with heavy-gauge straps for long-lasting performance. Screw-pressure-plate back wiring (which also supports side wiring) enables fast installation and rock-solid connections.


Features & Benefits

Auto-ground on strap speeds up installation and holds mounting screws in position

Impact-resistant polycarb back body and frame, for structural strength and impact resistance

Cushioned thermoplastic paddle assures smooth, quiet long-term operation

Heavy-gauge steel strap is plated for corrosion resistance



Single rocking butterfly contact design has fewer moving parts — for longer life, and smoother, quieter operation

Oversized silver alloy contacts integrally formed to the butterfly spring — assures high reliability

Tri-drive brass terminal screws, internal screw-pressure-plate back and side wire capability

Common terminal has two back wire holes for more wiring flexibility

2601W

3rd Party Compliance



UL Listed, File Number E140597, Standard UL20, General Use Snap Switches.
CSA Certified, File Number LR17446, Standard CSA-C22.2 No. 111, General Use Snap Switches.

Technical Information

Performance

Electrical

| | |
|------------------------------|--------------------------------------------------------------------------|
| Dielectric Withstand Voltage | 1500V Minimum |
| Maximum Working Voltage | 277VAC |
| Overload | Minimum 4.8 times rated current for 100 cycles |
| Temperature Rise | 30°C maximum at rated current |
| Maximum Continuous Current | 277VAC |
| Endurance | 10,000 cycles minimum, resistive, inductive, tungsten filament lamp load |

Mechanical


| | |
|-------------------------|-------------------|
| Terminal Accommodations | #14 AWG – #10 AWG |
|-------------------------|-------------------|

Environmental

| | |
|--------------|---------|
| Flammability | UL94 V2 |
|--------------|---------|

Materials

| | |
|-----------------|------------------------------|
| Back Body | Polycarbonate |
| Frame | Polycarbonate |
| Paddle | Thermoplastic |
| Terminals | Brass |
| Terminal Screws | Tri-Drive Brass-Plated Steel |
| Strap | Steel |
| Pressure Plate | Steel |
| Contacts | Silver Cadmium Oxide |
| Spring Arm | Brass |
| Bumper | Rubber |
| Spring | Zinc-Plated Steel |
| Ground Terminal | Brass |
| Ground Screw | Tri-Drive Zinc-Plated Steel |



Warranty

1 Year

Ordering Information

Decorator Switches Back & Side Wire


| Catalog Number | | | | Rating | | Color |
|----------------|-------------|-----------|----------|--------|---------|--------------|
| Single Pole | Double Pole | Three-Way | Four-Way | A | VAC | |
| 2601I | — | 2603I | 2604I | 15 | 120/277 | Ivory |
| 2601W | — | 2603W | 2604W | 15 | 120/277 | White |
| 2601GRY | — | 2603GRY | — | 15 | 120/277 | Gray |
| 2601BK | — | 2603BK | — | 15 | 120/277 | Black |
| 2601LA | — | 2603LA | 2604LA | 15 | 120/277 | Light Almond |
| 2621I | 2622I | 2623I | 2624I | 20 | 120/277 | Ivory |
| 2621W | 2622W | 2623W | 2624W | 20 | 120/277 | White |
| 2621 | 2622 | 2623 | 2624 | 20 | 120/277 | Brown |
| 2621GRY | 2622GRY | 2623GRY | 2624GRY | 20 | 120/277 | Gray |
| 2621BK | 2622BK | 2623BK | 2624BK | 20 | 120/277 | Black |
| 2621RED | 2622RED | 2623RED | 2624RED | 20 | 120/277 | Red |
| 2621LA | 2622LA | 2623LA | 2624LA | 20 | 120/277 | Light Almond |

Vertical Markets

- Education
- Institutional
- Retail
- Office
- Hospitality/Lodging
- Multiple Dwelling

Also available

- Plug Load Solutions
- Hospital Grade Devices
- PlugTail® Devices
- Surge Protective Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- USB Charging Devices
- Flexcor® Wire Mesh Grips
- Chemical-Resistant Switches

 The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act compliant. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
905.738.9195
www.legrand.ca

FOLLOW US





Smooth style and operation — plus commercial durability.

2601, 2603, 2604, 2621, 2622, 2623, 2624

Cushioned thermoplastic paddles assure smooth, quiet long-term use. Integral silver-alloy contacts combine with heavy-gauge straps for long-lasting performance. Screw-pressure-plate back wiring (which also supports side wiring) enables fast installation and rock-solid connections.


Features & Benefits

Auto-ground on strap speeds up installation and holds mounting screws in position

Impact-resistant polycarb back body and frame, for structural strength and impact resistance

Cushioned thermoplastic paddle assures smooth, quiet long-term operation

Heavy-gauge steel strap is plated for corrosion resistance



Single rocking butterfly contact design has fewer moving parts — for longer life, and smoother, quieter operation

Oversized silver alloy contacts integrally formed to the butterfly spring — assures high reliability

Tri-drive brass terminal screws, internal screw-pressure-plate back and side wire capability

Common terminal has two back wire holes for more wiring flexibility

2601W

3rd Party Compliance



UL Listed, File Number E140597, Standard UL20, General Use Snap Switches.

CSA Certified, File Number LR17446, Standard CSA-C22.2 No. 111, General Use Snap Switches.

Technical Information

Performance

Electrical

| | |
|------------------------------|--------------------------------------------------------------------------|
| Dielectric Withstand Voltage | 1500V Minimum |
| Maximum Working Voltage | 277VAC |
| Overload | Minimum 4.8 times rated current for 100 cycles |
| Temperature Rise | 30°C maximum at rated current |
| Maximum Continuous Current | 277VAC |
| Endurance | 10,000 cycles minimum, resistive, inductive, tungsten filament lamp load |

Mechanical


| | |
|-------------------------|-------------------|
| Terminal Accommodations | #14 AWG – #10 AWG |
|-------------------------|-------------------|

Environmental

| | |
|--------------|---------|
| Flammability | UL94 V2 |
|--------------|---------|

Materials

| | |
|-----------------|------------------------------|
| Back Body | Polycarbonate |
| Frame | Polycarbonate |
| Paddle | Thermoplastic |
| Terminals | Brass |
| Terminal Screws | Tri-Drive Brass-Plated Steel |
| Strap | Steel |
| Pressure Plate | Steel |
| Contacts | Silver Cadmium Oxide |
| Spring Arm | Brass |
| Bumper | Rubber |
| Spring | Zinc-Plated Steel |
| Ground Terminal | Brass |
| Ground Screw | Tri-Drive Zinc-Plated Steel |



Warranty

1 Year

Ordering Information

Decorator Switches Back & Side Wire


| Catalog Number | | | | Rating | | Color |
|----------------|-------------|-----------|----------|--------|---------|--------------|
| Single Pole | Double Pole | Three-Way | Four-Way | A | VAC | |
| 2601I | — | 2603I | 2604I | 15 | 120/277 | Ivory |
| 2601W | — | 2603W | 2604W | 15 | 120/277 | White |
| 2601GRY | — | 2603GRY | — | 15 | 120/277 | Gray |
| 2601BK | — | 2603BK | — | 15 | 120/277 | Black |
| 2601LA | — | 2603LA | 2604LA | 15 | 120/277 | Light Almond |
| 2621I | 2622I | 2623I | 2624I | 20 | 120/277 | Ivory |
| 2621W | 2622W | 2623W | 2624W | 20 | 120/277 | White |
| 2621 | 2622 | 2623 | 2624 | 20 | 120/277 | Brown |
| 2621GRY | 2622GRY | 2623GRY | 2624GRY | 20 | 120/277 | Gray |
| 2621BK | 2622BK | 2623BK | 2624BK | 20 | 120/277 | Black |
| 2621RED | 2622RED | 2623RED | 2624RED | 20 | 120/277 | Red |
| 2621LA | 2622LA | 2623LA | 2624LA | 20 | 120/277 | Light Almond |

Vertical Markets

- Education
- Institutional
- Retail
- Office
- Hospitality/Lodging
- Multiple Dwelling

Also available

- Plug Load Solutions
- Hospital Grade Devices
- PlugTail® Devices
- Surge Protective Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- USB Charging Devices
- Flexcor® Wire Mesh Grips
- Chemical-Resistant Switches

 The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act compliant. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
905.738.9195
www.legrand.ca

FOLLOW US

