



# 289 Series (Mogul Base) SpringLamp® Specification

<b>Compact Fluorescent</b>	<b>NPF – 10,000 Hours</b>
----------------------------	---------------------------

### Applications:

**Perfect for most applications:** Use where a standard incandescent is used.

- + High Bays
- + Low Bays
- + Open Fixtures
- + Parking Lots
- + Warehouses

### Special Application Options: (Ordering Suffix)

- 3000°K (30K), 3500°K (35K), 4100°K (41K), 5000°K (50K), 6500°K (65K)
- Long Neck 1.65" (165), 1.75" (175), 2.25" (225)
- Shatter Resistant (68 watt can NOT be shatter resistant)

### Features and Benefits:

- Long life CFL, 10,000 hour average rated life.
- NEW Amalgam technology- provides cooler operating temperatures for consistent performance in any position.
- No lead glass – Better lumen maintenance over life of bulb.
- 2700°K color temperature closest to incandescent light.
- Medium / mogul base available.
- Replace less often, ideal for hard to reach places.
- Quickstart technology – fast run up time



28927H  
28927H277




28932H  
28932H277



28942H  
28942H277



28968H  
28968H277



### Specifications: ( at full brightness )

End of Life Protection .....	Yes
Ballast Type .....	Electronic
Starting Method .....	Modified Rapid Start
Input Line Voltage .....	120 or 277V
Input Line Frequency .....	50/60HZ
Color Temperature .....	2700°K
Color Rendering Index .....	82
Minimum Starting Temperature .....	-20°F, -29°C
Maximum Operating Temperature .....	160°F, 71°C
U.L. / C.U.L. Listed .....	Yes
FCC Compliance .....	Part 18, Subpart C
Lamp Operating Frequency .....	45 KHZ
Lamp Current Crest Factor .....	<1.60
Total Harmonic Distortion .....	<150%
Power Factor Rated .....	>.50

### Special Application Notes:

Up to 23 watt is UL approved for totally enclosed fixtures.

Use a 27w and 32w in an open recessed can

Do not use a 27w and 32w in an enclosed recessed can. Use voids the warranty.

Do not use a 42w and 68w in an enclosed or open recessed can or any type of enclosed fixture. Use voids the warranty.

Warranties and Certifications:	Item #	Wattage	Incandescent Wattage Comparison	Initial Lumens	Input Line Current	M.O.L (inches)	Diameter (inches)	Lamp Life (hours)
	28927H	27	100	1850	.45A	6.2	2.8	13X
	28927H277	27	100	1850	.19A	6.2	2.8	13X
	28927277	27	100	1850	.19A	6.0	2.8	13X
	28932H	32	120	2200	.53A	6.6	2.8	13X
	28932H277	32	120	2200	.23A	6.6	2.8	13X
	28932277	32	120	2200	.23A	6.0	2.8	13X
	28942H	42	150	2800	.70A	7.0	2.8	13X
	28942H277	42	150	2800	.30A	7.0	2.8	13X
	28942277	42	150	2800	.30A	7.0	2.8	13X
	28968H	68	300	4200	1.13A	9.8	4.1	13X
	28968H277	68	300	4200	.49A	9.8	4.1	13X
	28968277	68	300	4200	.49A	9.5	4.1	13X





# 289 Series (Mogul Base) SpringLamp® Specification

**Compact Fluorescent**

**NPF – 10,000 Hours**

**Applications:**

**Perfect for most applications:** Use where a standard incandescent is used.

- + High Bays
- + Low Bays
- + Open Fixtures
- + Parking Lots
- + Warehouses

**Special Application Options: (Ordering Suffix)**

- 3000°K (30K), 3500°K (35K), 4100°K (41K), 5000°K (50K), 6500°K (65K)
- Long Neck 1.65" (165), 1.75" (175), 2.25" (225)
- Shatter Resistant (68 watt can NOT be shatter resistant)

**Features and Benefits:**

- Long life CFL, 10,000 hour average rated life.
- NEW Amalgam technology- provides cooler operating temperatures for consistent performance in any position.
- No lead glass – Better lumen maintenance over life of bulb.
- 2700°K color temperature closest to incandescent light.
- Medium / mogul base available.
- Replace less often, ideal for hard to reach places.
- Quickstart technology – fast run up time



28927H  
28927H277



28932H  
28932H277



28942H  
28942H277



28968H  
28968H277

Catalog Number

Notes

Type



**Specifications: ( at full brightness )**

End of Life Protection .....	Yes
Ballast Type .....	Electronic
Starting Method .....	Modified Rapid Start
Input Line Voltage .....	120 or 277V
Input Line Frequency .....	50/60HZ
Color Temperature .....	2700°K
Color Rendering Index .....	82
Minimum Starting Temperature .....	-20°F, -29°C
Maximum Operating Temperature .....	160°F, 71°C
U.L. / C.U.L. Listed .....	Yes
FCC Compliance .....	Part 18, Subpart C
Lamp Operating Frequency .....	45 KHZ
Lamp Current Crest Factor .....	<1.60
Total Harmonic Distortion .....	<150%
Power Factor Rated .....	>.50

**Special Application Notes:**

Up to 23 watt is UL approved for totally enclosed fixtures.

Use a 27w and 32w in an open recessed can

Do not use a 27w and 32w in an enclosed recessed can. Use voids the warranty.

Do not use a 42w and 68w in an enclosed or open recessed can or any type of enclosed fixture. Use voids the warranty.

**Warranties and Certifications:**

Item #	Wattage	Incandescent Wattage Comparison	Initial Lumens	Input Line Current	M.O.L (inches)	Diameter (inches)	Lamp Life (hours)
28927H	27	100	1850	.45A	6.2	2.8	13X
28927H277	27	100	1850	.19A	6.2	2.8	13X
28927277	27	100	1850	.19A	6.0	2.8	13X
28932H	32	120	2200	.53A	6.6	2.8	13X
28932H277	32	120	2200	.23A	6.6	2.8	13X
28932277	32	120	2200	.23A	6.0	2.8	13X
28942H	42	150	2800	.70A	7.0	2.8	13X
28942H277	42	150	2800	.30A	7.0	2.8	13X
28942277	42	150	2800	.30A	7.0	2.8	13X
28968H	68	300	4200	1.13A	9.8	4.1	13X
28968H277	68	300	4200	.49A	9.8	4.1	13X
28968277	68	300	4200	.49A	9.5	4.1	13X



**15 MONTH WARRANTY**



**PARTNER OF THE YEAR**