



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2LEDTRIMG2DC30K9 2" 3000K 90CRI Led Downlight Trim

Lithonia Lighting - Acuity

Catalog Number	2LEDTRIMG2DC30K9
Manufacturer	Lithonia Lighting - Acuity
Description	The Juno Recessed 2 In. Led Trim Features Die Cast Beveled Knife Edge Trim Ring For Clean Ceiling Interface.
Weight per unit	13.8 (lbs/each)
Product Category	20181012125812

Features

average life	50,000
Lamp Type	LED - Static
lumens	1000 LM,600 LM
Maximum Operating Temperature	25
Number of Lamps	1
Power Source	Hardwired
Shape	Round

Material, Color, and Finish

Color	White
color rendering index (cri)	90
color temperature	3000

Dimensions and Weight

Height	4.375
Length	3.125
Width	3.125

Descriptions

Construction	Canless,New Construction,Remodel
Description	2" 3000K 90CRI LED DOWNLIGHT TRIM
extra long description	LITH 2LEDTRIM G2 DC 30K 90CRI FL WW
Long Description	The Juno Recessed 2 in. LED Trim features die cast beveled knife edge trim ring for clean ceiling interface.
Product Type	Trim

Manufacturer Information

Brand	JUNO
GTIN	00661209587688
Manufacturers Part Number	2LEDTRIM G2 DC 30K 90CRI FL WW
UPC	661209587688

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
----------------------	--------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

aperture size 2 IN

Packaging

Carton 1

Weight 13.549

Weight Per each 13.844

Uses, Certifications, and Standards

Application Education, Government, Healthcare, Hospitality, House of
Worship, Offices & Banks, Residential, Retail

environmental conditions Indoor

Mounting Recessed