



## **RESI-MASTER™ Heavy-Duty Ship Augers**



- **Reinforced Cutting Edge**  
The 62° cutting angle reinforces the cutting edge and provides greater durability even after multiple nail strikes
- **Increased Life & Durability**  
The hardened lead screw and cutting edge provide increased wear resistance and extended life
- **Quick & Efficient Chip Removal**  
The secondary relief angle evacuates wood chips quickly and prevents the auger from jamming, even in wet or treated woods
- **Easy Bit Ejection**  
The oversized cutting head makes a hole larger than the body of the bit for easy ejection from the work piece



Efficient design quickly feeds through and ejects chips even in wet or treated woods without binding or jamming



# RESI-MASTER™ Heavy-Duty Ship Augers


- 62° reinforced cutting edge for added durability
- Precision ground, self-feeding lead screw
- Secondary relief angle for efficient chip removal
- Hardened lead screw and cutting edge powers through nails and staples and extends tool life
- Hardened & tempered shaft minimizes warping
- Quick-change shank design for fast bit changes and use with pneumatic drills

### Overall Length = 7-1/2", Twist = 5"


Cat. No.	UPC No. 783250	Hole Diameter	Overall Length	Twist Length
35-892	632862	5/8"	7-1/2"	5"
35-893	632879	3/4"	7-1/2"	5"
35-896	632909	7/8"	7-1/2"	5"
35-897	632916	15/16"	7-1/2"	5"
35-898	632923	1"	7-1/2"	5"
35-899	632930	1-1/8"	7-1/2"	5"

### Overall Length = 18", Twist = 15"

Cat. No.	UPC No. 783250	Hole Diameter	Overall Length	Twist Length
35-971	632947	5/8"	18"	15"
35-972	632954	3/4"	18"	15"
35-976	632961	7/8"	18"	15"
35-977	632978	15/16"	18"	15"
35-978	632985	1"	18"	15"
35-979	632992	1-1/8"	18"	15"



Quickly powers through multiple studs without binding or jamming, resulting in a clean, finished hole.



#### IDEAL INDUSTRIES, INC.

Becker Place, Sycamore, IL 60178, USA / 815-895-5181 • 800-435-0705 in USA  
 33 Fuller Road, Ajax, Ontario L1S 2E1, Canada / 905-683-3400 • 800-527-9105 in Canada  
 225 Europa Boulevard, Gemini Business Park, Warrington, Cheshire, WA5 7TN, UK / +44-(0) 1925 444446  
 Gutenbergstrasse 10, 85737 Ismaning, Germany / +49-(0) 89 996860  
 Level 6, 75-85 Elizabeth Street, Sydney NSW 2000 Australia / 61300 765 800  
 Prof. Americas 1600 4to Piso, Col. Country Club, Guadalajara, Jal. 44610 / 52-33-36789176  
 Av. Major Sylvio de M. Padilha, 5200 - 201/F, São Paulo - SP 05677-000 - Brazil / +55-11-3759-8777  
 Room 1401, Finance Square, 333 Jiujiang Road, Shanghai 2000001, China / 86-21-6360-7045  
 Unit 911, Tower W1, The Towers, Oriental Plaz, No. 1 East Chang An Avenue, Dong Cheng District  
 Beijing, 100738, China / Ph: 86-10-8518-3141

[www.idealindustries.com](http://www.idealindustries.com)

Form No. P-2677  
©2005 IDEAL INDUSTRIES, INC.

11/05  
Printed in U.S.A.