



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



36241012 Encl 10X24X36 N12 CH CLMP CVR *Cooper B-Line/Cable Tray*

| | |
|------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | 36241012 |
| Manufacturer | Cooper B-Line/Cable Tray |
| Description | Eaton B-Line Series Wall Mounted Panel Enclosure, 36" Height, 10" Length, 24" Width, Nema 12, Hinged Cover, 12 Enclosure, Wall Mount, Medium Single Door, External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket |
| Weight per unit | 67.6 (lbs/each) |
| Product Category | Nema Types 12 & 13 Metallic En |

Features

| | |
|---------------|--------------------------------------|
| dimensions | 10.0000 IN X 24.0000 IN X 36.0000 IN |
| Mounting Type | Wall |

Material, Color, and Finish

| | |
|-------|------|
| Color | Gray |
|-------|------|

Dimensions and Weight

| | |
|------|---------------------------------------------------|
| Size | 24.00 In Width X 10.00 In Depth X 36.00 In Height |
|------|---------------------------------------------------|

Descriptions

| | |
|------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | ENCL 10X24X36 N12 CH CLMP CVR |
| extra long description | B-LINE 362410-12 TYPE 12 SGL-DOOR E |
| Features | Eaton's B-Line series JIC wall mount, ground mount and terminal Type 12 panel enclosures are used to house electrical controls and instruments while helping protect them against circulating dust, falling dirt and dripping non-corrosive liquids. |
| Long Description | Eaton B-Line series wall mounted panel enclosure, 36" height, 10" length, 24" width, NEMA 12, Hinged cover, 12 enclosure, Wall mount, Medium single door, External mounting feet, Carbon steel, Seamless poured in-place gasket |
| Product Type | Type 12 SGL-Door Enc, 36X24X10 |
| Special Features | Plated door clamps |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00782051803501 |
| Manufacturers Part Number | 362410-12 |
| UPC | 782051803501 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------|
| Category Description | STEEL JUNCTION BOXES |
| Type | Type 12 panel enclosures |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Weight Per each | 67.59 |

Uses, Certifications, and Standards

| | |
|-------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Application | Commercial / Institutional Buildings / Structures - Power Distribution and Controls Datacenters - IT Space: CI and Hyper Converged Commercial / Institutional Buildings / Structures - Safety and Security Systems Commercial / Institutional Buildings / Structures - Lighting and Lighting Controls Commercial / Institutional Buildings / Structures - Critical Power Utility - Substations, Utility Transmission and Distribution Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures |
| Mounting standard | EXTERNAL FEET, WALL CSA C22.2, NEMA, UL 508A |