


## Steel - Rigid/Liquidtight Transition - Raintight

### Images



### Application

For creating a Liquidtight/Raintight Connection between 2 different Raceways: 1" Rigid Conduit (GRC &&& IMC) and 1" Liquidtight Flexible Metallic Conduit (LFMC). Suitable for use in wet locations. Concrete Tight

### Product Information

Material: Malleable Iron  
Finish: Zinc Coated

### Certifications & Codes:

CSA File Number:	cULus
Federal Specification Number:	A-A-50553A
NEMA Standard:	FB-1
UL File Number:	E9391
UL Standard:	514B
UNSPSC:	39131707

[Download Photo Image](#)   [Download Dimensional Image](#)  
Dimension A in Inches: 1  
Dimension B in Inches: 13/16  
Dimension C in Inches: 1-7/8

**Catalog ID:** 4372-LT

**UPC Number:** 78174720372

**Description:** Combination Coupling for transitioning between 1" Liquidtight Flexible Metallic Conduit (LFMC) and 1" Rigid Steel Conduit. NPSM Threads on Hub. Malleable Iron Body with Steel Ferrule

**Application:** For creating a Liquidtight/Raintight Connection between 2 different Raceways: 1" Rigid Conduit (GRC &&& IMC) and 1" Liquidtight Flexible Metallic Conduit (LFMC). Suitable for use in wet locations. Concrete Tight

**Trade Size:** 1"

**Std Pkg Qty:** 25

**Unit Qty:** 5