



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 4Q300 3" Sealtight Straight Steel Connector *Appleton/Oz Gedney*

Catalog Number	4Q300
Manufacturer	Appleton/Oz Gedney
Description	Oz-Gedney Type 4Q Liquid Tight Straight Connector, Size: 3 In, Connection: Tapered MNPT Hub, Malleable Iron Body and Nut, Steel Ferrule, Finish: Zinc Electroplated, Nema Rating: Nema 4, 4-7/8 In Width, 3-1/8 In Height, Third Party Certification: UI
Weight per unit	3.5 (lbs/each)
Product Category	Liquid Tight Fittings

### Features

connection	Tapered MNPT Hub
Material	Malleable Iron Body And Nut, Steel Ferrule

### Material, Color, and Finish

Finish	Zinc Electroplated
--------	--------------------

### Dimensions and Weight

Size	3
------	---

### Descriptions

Description	3" SEALTIGHT STRAIGHT STEEL CONNECTOR
extra long description	OZG 4Q-300 3 IN STR CONN LFMC
Long Description	OZ-Gedney Type 4Q Liquid Tight Straight Connector, Size: 3 IN, Connection: Tapered MNPT Hub, Malleable Iron Body And Nut, Steel Ferrule, Finish: Zinc Electroplated, NEMA Rating: NEMA 4, 4-7/8 IN Width, 3-1/8 IN Height, Third Party Certification: UL
Product Type	3 In STR Conn LFMC
Special Features	4Q fittings have plain throat (non-insulated);Bonding wedge locknuts are recommended in hazardous locations;Compact, slim diameter with small turning radius;Furnished with locknut and knockout sealing ring;Hot dip or mechanically galvanized finish optionally available;Inspection windows in ferrule to ensure full en;Intrinsically safe;Liquidtight/raintight/oiltight/concretetight;Long ferrule prevents pullout and tight bend conduit pop-out;O-Z/Gedney fittings are used with liquidtight flexible metal conduit

### Manufacturer Information

Brand	O-Z/GEDNEY
GTIN	00783126617955
Manufacturers Part Number	4Q-300
UPC	783126617955



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description METALLIC FITTINGS

Type Type 4Q Liquid Tight Straight Connector

## Packaging

Carton 5

Weight Per each 3.5

## Uses, Certifications, and Standards

Application For Liquidtight Flexible Metal Conduit

nema rating 4

standard Third Party Certification: UL File Number 11853, CSA 009795,  
Applicable Third Party Standards: UL 514B, CSA C22.2 No.18,  
Federal Specification W-F-406E, NEMA : FB-1, Hazardous  
Locations: Class I, Division 2 Per NEC 501.4(B), Class I, Zone 2 Per  
NEC 505.15(C)(2), Class II, Division 1 Per NEC 502.4(A)(1)(e), Class  
II, Division 2 Per NEC 502.4(B)(2), Class III, Division 1 Per NEC  
503.3(A)(2), Class III, Division 2 Per NEC 503.3(B), Intrinsically  
Safe Per NEC 504.20