



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



5249 BX Steel 10-3 250FT Coil (AC90) *Southwire Company*

Catalog Number	5249
Manufacturer	Southwire Company
Description	10-3 Solid Black, Red, White - Ac-90® Black Interlocked Galvanized Steel Armor W/Phase Id - Type Ac - 125' Coil
Weight per unit	38.3 (lbs/ft)
Product Category	Teck

Features

Bend Radius	9.0
Conductor Size	10
gauge	10 AWG
Inside Diameter	0.4
Material	Galvanized Steel
Number of Conductors	3
outside diameter	0.6
Voltage Rating	600V

Material, Color, and Finish

Color	Black
Conductor Material	Copper
Finish	Black Paint

Dimensions and Weight

Length	1500
--------	------

Descriptions

Description	BX STEEL 10-3 250FT COIL (AC90)
extra long description	AFC 1408N32-00 *10-3 ACS 125C
Features	AC-90® Cables from Atkore, sometimes referred to as BX cable, are a commercial wiring method favored by installers for their flexible interlocked steel armor, which provides mechanical protection. These versatile 600V cables with THHN conductors have certain construction limitations due to the inception and design of UL Standard 4 over 100 years ago. The UL Standard allows for 2, 3, or 4 conductors, individually wrapped with moisture-resistant, fire-retardant paper and twisted from 14 AWG to 1 AWG. Type AC
Long Description	10-3 Solid Black, Red, White - AC-90® Black Interlocked Galvanized Steel Armor w/Phase ID - Type AC - 125' Coil
Product Type	*10-3 Acs 125C
Short Description	*10-3 ACS 125C



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Flexible Conduit
GTIN	00077680201829
Manufacturers Part Number	1408N32-00
UPC	077680201829

Taxonomies, Classifications, and Categories

Category Description	BX & MC
Type	AC-90® Steel Armored Cable Type AC

Trade Size

Trade Size	10-3
------------	------

Packaging

Carton	1
Weight	1615.68
Weight Per foot	38.3

Uses, Certifications, and Standards

standard	UL 4, 83, 1479, 1581, 2556 File Number E7330, NEC 250.118(8), 300.22(C), 392, 320, 517.13, 518, 645, Federal Specification A-A-59544 (Formerly J-C-30B), Meets OSHA And HUD Requirements
Temperature Rating	194