

SPECIALTY SEALANT CAULKS

RectorSeal® RS 136

Fire block / smoke seal caulk

Code	Description	Qty.
66408	10.3 oz. cartridge	12



FEATURES

- Easy application
- Interior applications
- Water Clean-up
- ASTM E 136 compliant

Application • General purpose, residential acoustical fireblock

Recommended for

- Electrical • Plumbing • Plastic pipe
- Telephone communication systems penetrations



RectorSeal® Silicone Sealant

General purpose

Code	Description	Qty.
57505	10.3 oz. tube - white	12
57506	10.3 oz. tube - clear	12

FEATURES

- Remains flexible
- Vibration resistant
- Indoors/outdoor

Application • Ideal for general sealing

- Dries to touch in 30 minutes and fully cures in 24 hours

Recommended for

- Around electrical panels • Windows • Doors
- Pipes/vents • Corner joints • Aluminum siding
- Other interior / exterior building materials



RectorSeal® Hi-Temp™

100% RTV silicone caulk

Code	Description	Qty.
57500	10.1 oz. cartridge	24

FEATURES

- One component
- USDA specs for use in federally inspected meat and poultry plants
- F.D.A. reg #21 CFR 177.2600
- TT-S-001543A (COM-NBS) Class A
- TT-S00230C (COM-NBS) Class AA
- MIL-A-46106B Amend 3, Type 1
- Canadian 19-GP-9MA, Type 1

Application • Cures to a strong durable resilient rubber

- Recommended for** • Glass • Clean metal • Most types of non-oily wood • Vulcanized silicone rubber • Silicone resins
- Natural and synthetic fiber • Ceramic • Paper
 - Many painted and plastic surfaces



SPECIALTY SEALANT CAULKS

RectorSeal® RS 136

Fire block / smoke seal caulk

Code	Description	Qty.
66408	10.3 oz. cartridge	12



FEATURES

- Easy application
- Interior applications
- Water Clean-up
- ASTM E 136 compliant

Application • General purpose, residential acoustical fireblock

Recommended for

- Electrical • Plumbing • Plastic pipe
- Telephone communication systems penetrations



RectorSeal® Silicone Sealant

General purpose

Code	Description	Qty.
57505	10.3 oz. tube - white	12
57506	10.3 oz. tube - clear	12

FEATURES

- Remains flexible
- Vibration resistant
- Indoors/outdoor

Application • Ideal for general sealing

- Dries to touch in 30 minutes and fully cures in 24 hours

Recommended for

- Around electrical panels • Windows • Doors
- Pipes/vents • Corner joints • Aluminum siding
- Other interior / exterior building materials



RectorSeal® Hi-Temp™

100% RTV silicone caulk

Code	Description	Qty.
57500	10.1 oz. cartridge	24

FEATURES

- One component
- USDA specs for use in federally inspected meat and poultry plants
- F.D.A. reg #21 CFR 177.2600
- TT-S-001543A (COM-NBS) Class A
- TT-S00230C (COM-NBS) Class AA
- MIL-A-46106B Amend 3, Type 1
- Canadian 19-GP-9MA, Type 1

Application • Cures to a strong durable resilient rubber

- Recommended for** • Glass • Clean metal • Most types of non-oily wood • Vulcanized silicone rubber • Silicone resins
- Natural and synthetic fiber • Ceramic • Paper
 - Many painted and plastic surfaces

