



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



61521 3-Phase/Motor Rotation Tester

Ideal

Catalog Number	61521
Manufacturer	Ideal
Description	3-Phase/Motor Rotation Tester, Voltage Rating: 100 - 600 Vac (10 - 400 HZ) Nominal For Phase Presence Indication, Amperage Rating: 18 Milamp Maximum Consumption, 3 PH Phase, Temperature Rating: 5 - 131 Deg F Operating, -4 to 158 Deg F Storage, Display: Neon Lamps and Leds, Dimensions: 6 In Height X 2.8 In Width X 1.4 In Depth, Phase Rotary Field Direction: 1 - 600 Vac (2 - 400 HZ), Determination Of Motor Rotation: 1 - 600 Vac (2 - 400 HZ) Requires Greater Than 1/2 Turn, Over Load Protection: 550 V (Between
Weight per unit	1.1 (lbs/each)
Product Category	Testers & Accessories

Features

amperage rating	18 MILAMP Maximum Consumption
dimensions	6 IN Height X 2.8 IN Width X 1.4 IN Depth
display	Neon Lamps And LEDs
Phase	3 Ph
Voltage Rating	100 - 600 VAC (10 - 400 HZ) Nominal For Phase Presence Indication



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	3-PHASE/MOTOR ROTATION TESTER
extra long description	IDEAL 61-521 3 PHASE MOTOR ROTATION
Features	Identifies three-phase sequencesIndicates motor rotationChecks for open phasesFor use up to 600V2-year warranty
Long Description	3-Phase/Motor Rotation Tester, Voltage Rating: 100 - 600 VAC (10 - 400 HZ) Nominal For Phase Presence Indication, Amperage Rating: 18 MILAMP Maximum Consumption, 3 Ph Phase, Temperature Rating: 5 - 131 DEG F Operating, -4 To 158 DEG F Storage, Display: Neon Lamps And LEDs, Dimensions: 6 IN Height X 2.8 IN Width X 1.4 IN Depth, Phase Rotary Field Direction: 1 - 600 VAC (2 - 400 HZ), Determination Of Motor Rotation: 1 - 600 VAC (2 - 400 HZ) Requires Greater Than 1/2 Turn, Over Load Protection: 550 V (Between
Product Type	3 Phase Motor Rotation Tester
Special Features	Identifies three-phase sequence; Indicates motor rotation; Checks for open phases; For use up to 600 V; Meets IEC-1010 (EN61010) safety requirements; 2-year warranty; Includes carrying case

Manufacturer Information

Brand	Ideal
GTIN	00783250615216
Manufacturers Part Number	61-521
sub brand	Ideal
UPC	783250615216

Taxonomies, Classifications, and Categories

Category Description	TEST EQUIPMENT, TESTERS AND MULTIMETERS
Type	3-Phase/Motor Rotation Tester

Packaging

Carton	1
Weight Per each	1.05

Uses, Certifications, and Standards

standard	Meets IEC-1010 (EN61010) Safety Requirements, CE N12966, CAT III 600V
Temperature Rating	5 - 131 DEG F Operating, -4 To 158 DEG F Storage