

Model 700 Hand-Held Power Drive



Optional Carrying Case



Threading using a pipe wrench as a support arm



Capacity

- Pipe: 1/8"-2" (3 mm-50 mm).
Bolt: 1/4"-1" (6 mm-25 mm) using OO-RB Die Heads.

Features

- Heavy-duty hand-held power drive.
- Designed for RIDGID® No. 12-R die heads. Other RIDGID die heads (OO-R, OO-RB, 11-R) using adapters. Also used with 258/258XL pipe cutters. Die heads not included, see page 4.5.
- Approved by CSA to CSA and UL standards (115V only).

Technical Specifications

- Weight: 25 lbs. (11 kg) Power Drive only.
- Length: 28 1/4" (71.7 cm).
- Motor: Universal, 1/2 HP, 115V or 230V 50/60 Hz.
- Switch: Double-throw reversible.
- Gear Head: Spur gear reduction face gear drive. Spring-loaded adapter pawls. Hardened steel spindle gear.
- Body: Cast aluminum.
- Spindle Speed: 26-30 RPM (no load).

Selection

Catalog No.	Model No.	Description	Pipe Threading Capacity		Rod Threading Capacity		Max. Geared Threader Capacity		Weight	
			in.	mm	in.	mm	in.	mm	lb.	kg
41935	700	115V 50/60 Hz Only	1/8-2	3-50	1/4-1	6-25	6	150	25	11
41940	700	230V 50/60 Hz Only	1/8-2	3-50	1/4-1	6-25	6	150	25	11

Accessories

Catalog No.	Model No.	Accessories Description	Weight	
			lb.	kg
42600	770	Adapter for OO-R and OO-RB	3 3/8	2
42605	771	Adapter for O-R	3 3/8	2
42610	772	Adapter for 11-R	3 1/2	2
42615	773	Adapter for 111-R	3	1
42620	774	Square Drive Adapter - 1 5/16"	5 1/4	2
42625	775	Support Arm for No. 700	11	5
42950	B-171-X	Metal Carrying Case	29	13
10883	418	Oiler w/1 Gallon of Premium Thread Cutting Oil	20 1/2	9,4
41620	-	Gearhead Motor Grease	1	0,5



See page 4.12