

CONNECT AND PROTECT

Maximizing Your Grounding System



FROM GROUND RODS TO GROUND ENHANCEMENT MATERIAL (GEM): GET THE FACTS TO MAXIMIZE YOUR GROUNDING SYSTEM

To ensure you get the most out of your grounding system, you need to have all of the facts. Which ground rod should I choose? How will ground conditions affect my grounding system? How can I maximize my system's performance and save money, too? Turn to nVent ERICO for the support you need.

Copper-Bonded **Galvanized GROUND RODS: WHAT DO THE EXPERTS SAY?** Ground Rod **Ground Rod** There are a lot of factors to consider when determining which grounding system electrode is best for your specific · Cost-effective application. Do you select an electrode based solely on Lower purchase long service life price - not as cost? Or is your decision also influenced by longevity and cost-effective performance? over the expected life as Copper-If a lower purchase price is the only reason for selecting Copper-bonded bonded coating: an electrode, a galvanized steel rod is the way to go. · Permanent molecular Unfortunately, a galvanized steel rod is not the most costbond effective option due to its relatively short service life. Low resistance In 1995, the Fire Protection Research Foundation established Galvanized coating: performance the National Electrical Grounding Research Project (NEGRP) · Relatively short High fault current service life to document the performance of grounding system capacity (IEEE® Std 80) electrodes over time. The NEGRP evaluated Will not slip or · May crack if rod is bent the variation of grounding electrode earth tear when driven resistance at different geographic · Will not crack if rod is bent locations and explored the effects of 3.9 mil (99 micron) Copper coating several of the dominant variables over minimum coating may vary to meet a period of 10 years. required standards per ASTM® 123 The most extensive long term study 10 mil (254 micron) minimum coating on corrosion of buried copper and on rods listed to galvanized material was conducted UL®467 between 1910-1955 by the National Bureau of Standards. The result of this study was to determine relative corrosion rates, which help set the benchmark for the use of copper-bonded ground rods to this day. Carbon Steel When the electrodes at selected sites were core and tip*: exhumed for corrosion analysis and · Greater tensile strength * nVent ERICO copper-bonded observation, the results favored the use of · Deep driving capability and galvanized rods copper-bonded ground rods.

• The copper-bonded grounding electrodes showed minimal

· Galvanized steel ground rods exhibited a loss of zinc, which

corrosion when compared to galvanized rods

resulted in excessive steel corrosion



When an nVent ERICO brand of copper-bonded ground rod (top) and a copper-clad rod are subjected to the same pressure load, the inferior copper-clad rod (bottom) develops cracks and creases to the outer sheath. Damage to the rod negatively affects its serviceable life and puts the integrity of the entire electrode at risk.



Excavated after 12 years.

Top ground rod is galvanized steel, 3/4" x 10'. Bottom ground rod is copper-bonded, ⁵/₈" x 8'. Both ground rods were driven into the soil vertically at the Pecos testing site in Las Vegas, NV in December of 1992. Both ground rods were exhumed from the site in April of 2004.

The loss of zinc on the galvanized steel rod resulted in excessive corrosion of the steel. The copper-bonded steel ground rods showed minimal corrosion.



Excavated after 11 years.

This is a galvanized steel ground rod driven into the ground vertically at the Pawnee testing site in Las Vegas, NV. This ground rod was buried from May of 1992 until March of 2003. The loss of zinc resulted in excessive corrosion of the steel. One area is reduced from a 34" diameter to approximately a ¼" diameter due to the corrosion. The eventual failure would result in a potentially catastrophic loss of ground.

The nVent ERICO brand of copper-bonded ground rod has an electrolytic coating of copper deposited over a layer of nickel. This process helps ensure a long-lasting molecular bond between the copper layer and steel core. nVent recommends copper-bonded ground rods in most soil conditions, because the copper coating will not slip or tear when driven, nor will it crack if the rod is bent. Copper-bonded ground rods have a high tensile, carbon steel core, which is ideal for deep driving, and they provide a low resistance path to ground.

When compared to stainless steel or galvanized rods, copperbonded ground rods are a cost-effective option over the service life. It is important to note that certain soils and land fill areas may not be compatible with copper. In these situations, stainless steel rods can be used. However, the high cost of stainless steel rods often prohibits their widespread use.

THE BENEFITS OF GEM


The NEGRP report also positively supported the use of GEM for a grounding system. The report showed that vertical electrodes in GEM displayed minimal corrosion.

nVent ERICO brand of GEM can be applied around the conductors in a grounding system. GEM helps to reduce soil resistivity and lower ground impedance, which facilitates the dissipation of lightning energy into the earth mass. GEM is particularly useful in areas of moisture variation, sandy soils and rocky ground.


DON'T FORGET THE CONNECTIONS

Connections are often the most critical element of a grounding system, and subsequently can become the weak point due to aging and corrosion. The preferred method of connection is the nVent ERICO Cadweld exothermic welding process producing a molecular bond. The capacity of a grounding circuit to protect the safety of personnel depends on the quality of the connections made.

Ground Rod Life Expectancy



Ground Rod Annual Cost



REGULAR TESTING

To properly design a grounding system, it is essential to test soil resistivity. The most accurate method and the one that nVent recommends is the four-point method.


Soil resistivity should be tested before installing the ground electrode system, to make sure that the grounding system is meeting the IEEE®, NEC®, or local requirements. It is also recommended to test resistivity when expanding a building, adding significant amounts of electronics or telecommunications, installing or expanding a lightning protection system on a facility, or if the facility is experiencing problems with power quality. If the resistivity is not low enough, this may indicate that more ground rods are required.

TRUST YOUR SYSTEM TO AN EXPERT

The basic philosophy of a grounding installation should be to maximize the surface area contact of electrodes or conductors within the surrounding soil. Not only does this help to lower the earth resistance of the grounding system, but it also greatly improves the impedance of the grounding system under lightning surge conditions. It is recommended that some form of maintenance or inspection procedure be adopted to help ensure the long-term effectiveness of a grounding system.

nVent's products are designed and tested to meet the most demanding requirements available. Our electrodes (copper-bonded ground rods and accessories, such as couplers and connectors) comply with EN 50164-2. Certificates and test reports are available upon request.

The Cadweld Mold





Regular ground testing is highly recommended.

Trust nVent's expertise to help keep your system operating at its full potential.

Clamp-on

Grounding System Products

Copper-bonded Pointed Ground Rods						
US Part No.	Diameter (in.)	Length (ft.)	Europe Article No.	Reference Code	Diameter (mm)	Length (m)
615850	5/8	5	155240	12M58	14,2	1,2
615860	5/8	6	155250	15M58	14,2	1,5
615880*	5/8	8	155270	21M58	14,2	2,1
615800*	5/8	10	155290	30M58	14,2	3,0
613460	3/4	6	155420	12M34	17,2	1,2
613480*	3/4	8	155430	15M34	17,2	1,5
613400*	3/4	10	155450	21M34	17,2	2,1
614400*	1.0	10	155470	30M34	17,2	3,0

^{*} UL® Listed



Compression Couplers for Copper-bonded Pointed Ground Rods						
US Part No.	Diameter (in.)	Europe Article No.	Reference Code	Diameter (mm)		
CC58	5/8	158010	CC58	14,2		
CC34	3/4	158020	CC34	17,2		



Driving Sleeves for Copper-bonded Pointed Ground Rods						
US Part No.	Diameter (in.)	Europe Article No.	Reference Code	Diameter (mm)		
B137-16	5/8	158130	DT58	14,2		
B137-18	3/4	158140	DT34	17,2		
B137-22	1.0	_	_	_		



Ground Rod Clamps					
US Part No.	Conductor Range (in.)	Europe Article No.	Reference Code	Conductor Range Max. (mm²)	
CP58	10 Sol – 4 Str	158165	CP58	25	
CP34	8 Sol – 2 Str	158165	CP34	25	
SP58	10 Sol – 2 Str	158185	SP58	10 – 25	
GC064	4 Sol - 2/0 Str	710400	GUV16070	16 – 70	
GC065	2/0 Sol - 250 MCM	710410	GUV70185	70 – 185	



nVent ERICO Hammerlock − for Copper-bonded Ground Rod						
Global Part Number	Conductor Size Range - Imperial	Reference Code	Conductor Size Range - Metric	Ground Rod Size (in.)		
EHL58C2G	1/0 Str - 2/0 Str	EHL58C2G	50.0 mm ² Str – 70.0 mm ² Str	5/8		
EHL58C1V	4 Str - 2 Str	EHL58C1V	22.0 mm ² Str - 35.0 mm ² Str	5/8		
EHL58C1K	6 Sol – 4 Sol	EHL58C1K	10.0 mm ² Str – 16.0 mm ² Str	5/8		
EHL34C2G	1/0 Str - 2/0 Str	EHL34C2G	50.0 mm ² Str – 70.0 mm ² Str	3/4		
EHL34C1V	4 Str - 2 Str	EHL34C1V	22.0 mm ² Str - 35.0 mm ² Str	3/4		
EHL34C1K	6 Sol – 4 Sol	EHL34C1K	10.0 mm ² Str - 16.0 mm ² Str	3/4		

Grounding System Products

Copper-bonded Threaded Ground Rods							
US Part No.	Diameter (in.)	Length (ft.)	Europe Article No.	Reference Code	Diameter (mm)	Length (m)	
635830	5/8	3	155300	S12M58	14,2	1,2	
635840	5/8	4	155310	S15M58	14,2	1,5	
635850	5/8	5	155330	S21M58	14,2	2,1	
635860	5/8	6	155350	S30M58	14,2	3,0	
635880*	5/8	8	155480	S12M34	17,2	1,2	
635800*	5/8	10	155490	S15M34	17,2	1,5	
633480*	3/4	8	155510	S21M34	17,2	2,1	
633400*	3/4	10	155530	S30M34	17,2	3,0	
634400*	1.0	10	_	_	25,4	3,0	

^{*} UL® Listed



Threaded Couplers for Copper-bonded Threaded Ground Rods						
US Part No.	Diameter (in.)	Europe Article No.	Reference Code	Diameter (mm)		
CR58	5/8	158040	SC58	14,2		
CR34	3/4	158050	SC34	17,2		
CR100	1.0	_	_	_		



Driving Studs for Copper-bonded Threaded Ground Rods						
US Part No.	Diameter (in.)	Europe Article No.	Reference Code	Diameter (mm)		
DS58	5/8	158100	DS58	14,2		
DS34	3/4	158110	DS34	17,2		

This list is only a sampling of our available products. To see our full line of omit nVent ERICO products, visit nVent.com/ERICO. Due to a policy of continuous product development, specifications are subject to change without notice.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER



nVent.com/ERICO