Pass and Seymour

Single-Pole Combination Switch and Pilot Light, White

Part No. 692WG



Single-Pole, Single Pilot light, Combination Switch, 15A, 120/125As, White.

Features & Benefits

- Easily accessible break-off separate or common feed.
- Side wire #12 and #14 AWG.
- Grounding combination devices meet NEC Requirements.
- For covering patents, see www.legrand.us/patents.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Two devices fit into the space of one.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Satin	UPC Number	785007006117
Country Of Origin	Mexico	Material	Thermoplastic
Features	Combination	Switch Type	Pilot, Switch
Number of Switches	1	Application Sector	Hospitality, Residential
Wall Plate Included	No	Standard	UL20
Warranty Type	1-Year Limited Warranty	Type	Combination

Dimensions

Product Width US	1.32 in	Product Depth US	1.15 in
Product Height US	4.06 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes

Technical Information

Load Rating	15 A @ 120 VAC	Contact Configuration	N-O
Operating Cycles	30000	Connection Location	Side Only
Terminal Accommodation	#14 AWG - #12 AWG	Number of Gangs	1
Throw Type	Single Throw	Amperage	15 A
Number of Poles	Single Pole	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Voltage	120.0 V
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon	Environmental Conditions	Flammability: UL94 V2