

Insulated Screwdrivers and Nut Drivers

Features:



1000 V Klein insulated tools meet or exceed the IEC 60900 and ASTM F1505 standards, for insulated tools, and are clearly marked with the official 1000-volt rating symbol.



Hollow shafts make it possible to work on stacked circuit boards or other long bolt applications.

Cushion-Grip handles for greater torque and comfort.

Custom, US-made tool steel.

Durable, two layer, molded insulation.

Patented Tip-Ident® quickly identifies nut driver size.

Thick, exceptionally tough, high-dielectric white inner coating is bonded to the tool.

Bright orange outer coating is flame and impact resistant.



Insulated Screwdrivers

Insulated Phillips-Tip – Round-Shank Screwdrivers

Additional Features:

- Klein's profilated Phillips-tip provides a more consistent geometric symmetry than conventional Phillips-tip screwdrivers.
- Square-Recess tips are perfect for electrical, telephone and work in recessed holes and other tight spaces.



603-7-INS



661-7-INS

Cat. No.	Point Size	Shank Length	Overall Length
⊕ Insulated Phillips Tip			
633-4-INS	#1	4" (102 mm)	7-3/4" (197 mm)
603-4-INS	#2	4" (102 mm)	8-5/16" (212 mm)
603-7-INS	#2	7" (178 mm)	11-5/16" (288 mm)
633-7-INS	#3	7" (178 mm)	12-3/8" (315 mm)
● Insulated Cabinet Tip			
607-3-INS	3/32" (2.4 mm)	3" (76 mm)	6-3/4" (171 mm)
612-4-INS	1/8" (6 mm)	4" (102 mm)	7-3/4" (197 mm)
601-4-INS	3/16" (5 mm)	4" (102 mm)	7-3/4" (197 mm)
601-7-INS	3/16" (5 mm)	7" (178 mm)	10-3/4" (273 mm)
602-4-INS	1/4" (6 mm)	4" (102 mm)	8-5/16" (212 mm)
605-7-INS	1/4" (6 mm)	7" (178 mm)	11-5/16" (288 mm)
602-7-INS	5/16" (8 mm)	7" (178 mm)	12-3/8" (315 mm)
602-8-INS	3/8" (9.5 mm)	8" (204 mm)	13-3/8" (340 mm)

Cat. No.	Point Size	Shank Length	Overall Length
⊖ Insulated Square-Recess Tip			
661-4-INS	#1	4" (102 mm)	8-5/16" (212 mm)
661-7-INS	#1	7" (178 mm)	11-5/16" (288 mm) NEW!
662-4-INS	#2	4" (102 mm)	8-5/16" (212 mm)
662-7-INS	#2	7" (178 mm)	11-5/16" (288 mm) NEW!

All dimensions are in inches and (millimeters).

⚠WARNING: Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source.



⚠WARNING: Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

⚠WARNING: Do NOT use screwdrivers to pry or chisel.

⚠WARNING: Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

⚠WARNING: Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.

⚠WARNING: Because moisture, films, or other surface contaminants are conductive, Klein insulated tools must be kept clean, dry, and free of any surface contaminants.



Insulated Screwdriver Sets



2-Piece Insulated 4" Screwdriver Set

Additional Features:

- Includes one 1/4" cabinet tip and one #2 Phillips tip.



33532-INS

Cat. No.	Set Contains
33532-INS	

Cat. No.	Description	Shank Tip Width	Shank Length	Overall Length
602-4-INS	round-shank, cabinet-tip	1/4" (6 mm)	4" (102 mm)	8-5/16" (211 mm)
603-4-INS	round-shank, profilated Phillips-tip	#2	4" (102 mm)	8-5/16" (211 mm)

Insulated Nut Drivers

6" Insulated Hollow-Shaft Nut Drivers

Additional Features:

- Slimmer molded insulation with increased durability.
- Hollow shafts make it possible to work on stacked circuit boards or other long bolt applications.



646-5/8-INS

Cat. No.	Color Code	Hex Size	Overall Length
646-3/16-INS	black	3/16"	9-3/4" (248 mm)
646-1/4-INS	red	1/4"	9-3/4" (248 mm)
646-5/16-INS	yellow	5/16"	9-3/4" (248 mm)
646-11/32-INS	green	11/32"	9-3/4" (248 mm)
646-3/8-INS	blue	3/8"	10-5/16" (262 mm)

Cat. No.	Color Code	Hex Size	Overall Length
646-7/16-INS	brown	7/16"	10-5/16" (262 mm)
646-1/2-INS	red	1/2"	11-3/8" (289 mm)
646-9/16-INS	orange	9/16"	11-3/8" (289 mm)
646-5/8-INS	yellow	5/8"	11-3/8" (289 mm)

Insulated Skinning Knife

Insulated Lineman's Skinning Knife

Additional Features:

- Molded measuring marks on back of handle to help measure stripping length of wire.
- Large molded handle for an easier, more comfortable grip.
- Tough, tempered steel blade provides maximum sharpness and durability to withstand frequent cable scoring.



1571-INS

Cat. No.	Blade Length	Handle Color	Overall Length
1571-INS	2 3/8" (60 mm)	orange	8-3/4" (223 mm)

All dimensions are in inches and (millimeters).

⚠WARNING: Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source.



⚠WARNING: Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

⚠WARNING: Do NOT use screwdrivers to pry or chisel.

⚠WARNING: Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

⚠WARNING: Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.

⚠WARNING: Because moisture, films, or other surface contaminants are conductive, Klein insulated tools must be kept clean, dry, and free of any surface contaminants.



General-Purpose Insulated 22-Piece Tool Kit

- Case includes three pallets with custom-fitted pockets for each tool, piano-hinged cover has both a combination lock and two key-locked latches for security, storage space behind the pallets to keep important papers and accessory items.
- Inside dimensions:
7-3/4" W x 14-1/4" D x 8" H
(451 mm x 362 mm x 203 mm).
- Overall dimensions:
18-7/8" W x 15-3/8" D x 8-1/4" H
(479 mm x 391 mm x 210 mm).
- Replacement case (Cat. No. 33537) available.



33527

See individual tool listings for more details.

Cat. No.	Kit Contains	Weight
33527		24.30 lbs. (11 kg)
Cat. No.	Description	
D2000-9NE-INS	insulated side-cutting pliers	
12098-INS	insulated universal side-cutting pliers	
D2000-28-INS	insulated diagonal-cutting pliers	
D2000-48-INS	insulated diagonal-cutting pliers – angled head	
D203-8N-INS	insulated heavy-duty long-nose pliers – side-cutting	
D220-7-INS	insulated diagonal-cutting pliers – tapered nose	
D203-6-INS	insulated long-nose pliers – side-cutting	
D203-7-INS	insulated long-nose pliers – side-cutting	
601-4-INS	insulated cabinet-tip – round-shank screwdriver (3/16" x 4")	
601-7-INS	insulated cabinet-tip – round-shank screwdriver (3/16" x 7")	
612-4-INS	insulated cabinet-tip – round-shank screwdriver (1/8" x 4")	
602-4-INS	insulated cabinet-tip – round-shank screwdriver (1/4" x 4")	
602-7-INS	insulated cabinet-tip – round-shank screwdriver (5/16" x 7")	
602-8-INS	insulated cabinet-tip – round-shank screwdriver (3/8" x 8")	
633-4-INS	insulated Phillips-tip – round-shank screwdriver (#1 x 4")	
603-4-INS	insulated Phillips-tip – round-shank screwdriver (#2 x 4")	
633-7-INS	insulated Phillips-tip – round-shank screwdriver (#3 x 7")	
D502-10-INS	insulated pump pliers	
11045-INS	insulated wire stripper/cutter	
63050-INS	insulated high-leverage cable cutter	
1571-INS	insulated lineman's skinning knife	
1005-INS	insulated crimping/cutting tool	
33537	extra-sturdy, bright-yellow case	

All dimensions are in inches and (millimeters).

▲WARNING: Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source.



▲WARNING: Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

▲WARNING: Do NOT use screwdrivers to pry or chisel.

▲WARNING: Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

▲WARNING: Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.

▲WARNING: Because moisture, films, or other surface contaminants are conductive, Klein insulated tools must be kept clean, dry, and free of any surface contaminants.



Utility Insulated 13-Piece Tool Kit

- The custom case includes two pallets with custom-fitted pockets for each tool, piano-hinged case cover has both a combination lock and two key-locked latches for security, storage space behind the pallets to keep important papers and accessory items.
- Inside dimensions: 17-3/4" W x 14-1/4" D x 8" H (451 mm x 362 mm x 203 mm).
- Overall dimensions: 18-7/8" W x 15-3/8" D x 8-1/4" H (479 mm x 391 mm x 210 mm).
- Replacement case (Cat. No. 33535) available.



33525

Cat. No.	Kit Contains	Weight
33525		20.05 lbs. (9 kg)
Cat. No.	Description	
D2000-9NE-INS	insulated side-cutting pliers	
D2000-28-INS	insulated diagonal-cutting pliers	
D2000-48-INS	insulated diagonal-cutting pliers – angled head	
D203-8-INS	insulated heavy-duty long-nose pliers – side-cutting	
602-4-INS	insulated cabinet-tip – round-shank screwdriver (1/4" x 4")	
602-7-INS	insulated cabinet-tip – round-shank screwdriver (5/16" x 7")	
602-8-INS	insulated cabinet-tip – round-shank screwdriver (3/8" x 8")	
633-4-INS	insulated Phillips-tip – round-shank screwdriver (#1 x 4")	

Cat. No.	Description
603-4-INS	insulated Phillips-tip – round-shank screwdriver (#2 x 4")
633-7-INS	insulated Phillips-tip – round-shank screwdriver (#3 x 7")
63050-INS	insulated high-leverage cable cutter
D502-10-INS	insulated pump pliers
1571-INS	insulated lineman's skinning knife
33535	extra-sturdy, bright-yellow case

Utility Insulated 13-Piece Tool Kit

- The light, compact, soft roll-up carry case provides protective storage with custom-fitted pockets for each tool.
- Kit includes a padded, adjustable shoulder strap.
- Case dimensions:
Opened 24-1/2" x 24-1/2" (622 mm x 622 mm).
Closed 24-1/2" x 5-1/2" (622 mm x 140 mm).
- Replacement roll-up case (Cat. No. 33535SC) available.



33525SC

Cat. No.	Kit Contains	Weight
33525SC		9.75 lbs. (4.4 kg)
Cat. No.	Description	
D2000-9NE-INS	insulated side-cutting pliers	
D2000-28-INS	insulated diagonal-cutting pliers	
D2000-48-INS	insulated diagonal-cutting pliers – angled head	
D203-8-INS	insulated heavy-duty long-nose pliers – side-cutting	
602-4-INS	insulated cabinet-tip – round-shank screwdriver (1/4" x 4")	
602-7-INS	insulated cabinet-tip – round-shank screwdriver (5/16" x 7")	
602-8-INS	insulated cabinet-tip – round-shank screwdriver (3/8" x 8")	
633-4-INS	insulated Phillips-tip – round-shank screwdriver (#1 x 4")	

Cat. No.	Description
603-4-INS	insulated Phillips-tip – round-shank screwdriver (#2 x 4")
633-7-INS	insulated Phillips-tip – round-shank screwdriver (#3 x 7")
63050-INS	insulated high-leverage cable cutter
D502-10-INS	insulated pump pliers
1571-INS	insulated lineman's skinning knife
33535SC	roll-up soft case with shoulder strap

All dimensions are in inches and (millimeters).

⚠WARNING: Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source.



⚠WARNING: Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

⚠WARNING: Do NOT use screwdrivers to pry or chisel.

⚠WARNING: Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

⚠WARNING: Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.

⚠WARNING: Because moisture, films, or other surface contaminants are conductive, Klein insulated tools must be kept clean, dry, and free of any surface contaminants.



Insulated 8-Piece Tool Kits

- Highly durable, black nylon case features: coil-zipper closure, polypropylene handles, custom-fitted tool pockets.
- Overall case dimensions are:
15-1/2" W x 11" D x 2-1/2" H
(394 mm x 279 mm x 64 mm).
- Replacement case (Cat. No. 33536) available.



33529

See individual tool listings for more details.

Premium Insulated 8-Piece Tool Kit

Cat. No.	Kit Contains	Weight
33529		6.90 lbs. (3 kg)
Cat. No.	Description	
D2000-9NE-INS	insulated side-cutting pliers	
D2000-48-INS	insulated diagonal-cutting pliers	
D203-8N-INS	insulated heavy-duty long-nose pliers – side-cutting	
601-4-INS	insulated cabinet-tip – round-shank screwdriver (3/16" x 4")	
602-4-INS	insulated cabinet-tip – round-shank screwdriver (1/4" x 4")	
603-4-INS	insulated Phillips-tip – round-shank screwdriver (#2 x 4")	
63050-INS	insulated high-leverage cable cutter	
11055-INS	insulated wire stripper/cutter	
33536	heavy-duty polyester case	

Basic Insulated 8-Piece Tool Kit

Cat. No.	Kit Contains	Weight
33526		6.90 lbs. (3 kg)
Cat. No.	Description	
D213-9NE-INS	insulated side-cutting pliers	
D228-8-INS	insulated diagonal-cutting pliers	
D203-8N-INS	insulated heavy-duty long-nose pliers – side-cutting	
601-4-INS	insulated cabinet-tip – round-shank screwdriver (3/16" x 4")	
602-4-INS	insulated cabinet-tip – round-shank screwdriver (1/4" x 4")	
603-4-INS	insulated Phillips-tip – round-shank screwdriver (#2 x 4")	
63050-INS	insulated high-leverage cable cutter	
11045-INS	insulated wire stripper/cutter	
33536	heavy-duty polyester case	

All dimensions are in inches and (millimeters).

▲WARNING: Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source.



▲WARNING: Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

▲WARNING: Do NOT use screwdrivers to pry or chisel.

▲WARNING: Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

▲WARNING: Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.

▲WARNING: Because moisture, films, or other surface contaminants are conductive, Klein insulated tools must be kept clean, dry, and free of any surface contaminants.



9-Piece Insulated Screwdriver Kit

- Nine-piece insulated screwdriver assortment with three sizes of each tip style: cabinet, keystone, and Phillips.
- Highly durable, black nylon case features: coil-zipper closure, polypropylene handles, custom-fitted tool pockets, extra pocket is provided for storage of papers or other items.
- Overall dimensions: 5-1/2" W x 11" D x 2-1/2" H (394 mm x 279 mm x 64 mm)
- Replacement case (Cat. No. 33538) available.

See individual tool listings for more details.

Cat. No.	Kit Contains	Weight
33528		5.40 lbs. (2.4 kg)
Cat. No.	Description	
601-4-INS	insulated cabinet-tip – round-shank screwdriver (3/16" x 4")	
601-7-INS	insulated cabinet-tip – round-shank screwdriver (3/16" x 7")	
612-4-INS	insulated cabinet-tip – round-shank screwdriver (1/8" x 4")	
602-4-INS	insulated cabinet-tip – round-shank screwdriver (1/4" x 4")	
602-7-INS	insulated cabinet-tip – round-shank screwdriver (5/16" x 7")	
602-8-INS	insulated cabinet-tip – round-shank screwdriver (3/8" x 8")	
633-4-INS	insulated Phillips-tip – round-shank screwdriver (#1 x 4")	
603-4-INS	insulated Phillips-tip – round-shank screwdriver (#2 x 4")	
633-7-INS	insulated Phillips-tip – round-shank screwdriver (#3 x 7")	
33538	heavy-duty polyester case	



33528

Cushion-Grip Insulated 9-Piece Nut Driver Kits

- Nine-piece insulated nut driver assortment of popular sizes.
- Individually tested to exceed standards.
- Two layers of insulation provide protection against electric shock.
- Highly durable, black nylon case features: oil-zipper closure, polypropylene handles, custom-fitted tool pockets, extra pocket is provided for storage of papers or other items.
- Overall case dimensions are: 15" W x 12-3/4" L x 3-1/2" D (381 mm x 324 mm x 89 mm).
- Replacement case available Cat. No. 33534.

See individual tool listings for more details.

Cat. No.	Kit Contains	Weight
33524		6.00 lbs. (2.7 kg)
Cat. No.	Description	
646-3/16-INS	insulated 3/16" hollow shaft nut driver, 6" shaft	
646-1/4-INS	insulated 1/4" hollow shaft nut driver, 6" shaft	
646-5/16-INS	insulated 5/16" hollow shaft nut driver, 6" shaft	
646-11/32-INS	insulated 11/32" hollow shaft nut driver, 6" shaft	
646-3/8-INS	insulated 3/8" hollow shaft nut driver, 6" shaft	
646-7/16-INS	insulated 7/16" hollow shaft nut driver, 6" shaft	
646-1/2-INS	insulated 1/2" hollow shaft nut driver, 6" shaft	
646-9/16-INS	insulated 9/16" hollow shaft nut driver, 6" shaft	
646-5/8-INS	insulated 5/8" hollow shaft nut driver, 6" shaft	
33534	Custom heavy-duty Cordura® case	



33524

Cordura® is a registered trademark of INVISTA for durable fabrics.

All dimensions are in inches and (millimeters).

⚠WARNING: Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source.



⚠WARNING: Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

⚠WARNING: Do NOT use screwdrivers to pry or chisel.

⚠WARNING: Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

⚠WARNING: Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.

⚠WARNING: Because moisture, films, or other surface contaminants are conductive, Klein insulated tools must be kept clean, dry, and free of any surface contaminants.

