



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



696G Combo 2SW 1P+3W 15A 120/277V BN

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | 696G |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Single-Pole, 3-Way Double Combination Switch, 15A 120/277V, Ivory. |
| Weight per unit | 0.2400 (lbs/each) |
| Product Category | Combination Devices |

Features

| | |
|-----------------------|--|
| action | (1) SP & (1) 3W |
| actuator | Toggle |
| amperage rating | 15 |
| connection | Side wire |
| Contact Configuration | N-O |
| Contact Rating | 15amp, 120/277vac |
| operating cycles | 30000 |
| Poles | 1 & 3-Way |
| Voltage | 0.433 V |
| Voltage Rating | 0.433212996389892 |
| Wattage | Electrical power is expressed in Amps and Volts. |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Brown |
|-------|-------|

Dimensions and Weight

| | |
|------|--------------------------|
| Size | 1.32 L x 0.94 W x 4.06 H |
|------|--------------------------|

Descriptions

| | |
|------------------------|---|
| Description | COMBO 2SW 1P+3W 15A 120/277V BN |
| extra long description | P&S 696G COMBO 2SW 1P+3W 15A 120/27 |
| Long Description | Single-Pole, 3-way Double Combination Switch, 15A 120/277V, Ivory. |
| Product Type | Combo 2SW 1P+3W 15A 120/277V BN |
| Special Features | Easily accessible break-off for separate or common feed. Side wire #12 and #14 AWG. Two devices fit into the space of one. Grounding combination devices meet NEC Requirements. |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007006209 |
| Manufacturers Part Number | 696-G |
| UPC | 785007006209 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | Residential Switches |
| Type | COMBINATION |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.24 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Residential/Commercial |
| environmental conditions | Flammability: UL94 V2 |
| Mounting | WALL |
| Operating Temperature | Maximum continuous +60°C, minimum -30°C |
| standard | CULUS, UL20 |