

FEATURES & SPECIFICATIONS

INTENDED USE

For use with housings LC6, LI6, L7X, L7XR and LP6.

CONSTRUCTION

Aluminum white sphere.

Polyester powder coat paint.

40 degree vertical tilt standard.

350 degree horizontal rotation.

White finish has integral flange.

INSTALLATION

Socket to trim interface.

Retaining clips riveted to top of reflector hold trim inside housing.

Rough-ins with clips retain trims.

LISTINGS

UL Listed to US and Canadian safety standards.

Damp location listed.

WARRANTY

1-year limited warranty. Complete warranty terms located at

www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx

Actual performance may differ as a result of end-user environment and application.

Note: Specifications subject to change without notice.


Catalog Number
Notes
Type

6" Finishing Trim

6E1

PREMIUM EYEBALL

Narrow Flange



Specifications


Height: 6-1/2 (16.5)

Lamp opening: 5-7/8 (14.9)

Diameter: 7-5/8 (19.4)

Trim height when used with Non-IC incandescent rough-in

All dimensions are inches (centimeters) unless otherwise indicated.



ORDERING INFORMATION

For shortest lead times, configure product using **bolded options**.

Example: 6E1

6E1	
Series	Finish
6E1	(blank) White

Accessories: Order as separate catalog number.	
CRT6	6" goof ring, white

Housing Compatibility: Housing and trim ordered separately.			
Application	Source	Maximum wattage	Housing
IC	Incandescent	75 PAR30	LC6, LI6, L7X, L7XR
		65 BR30	
Non-IC	Incandescent	75 PAR30	LP6
		65 BR30	

6E1 6" Premium Eyeball Full Reflector Trim

For BR and PAR reflector lamps, see lamp manufacturer's published raw lamp data for photometrics.

FEATURES & SPECIFICATIONS

INTENDED USE

For use with housings LC6, LI6, L7X, L7XR and LP6.

CONSTRUCTION

Aluminum white sphere.

Polyester powder coat paint.

40 degree vertical tilt standard.

350 degree horizontal rotation.

White finish has integral flange.

INSTALLATION

Socket to trim interface.

Retaining clips riveted to top of reflector hold trim inside housing.

Rough-ins with clips retain trims.

LISTINGS

UL Listed to US and Canadian safety standards.

Damp location listed.

WARRANTY

1-year limited warranty. Complete warranty terms located at

www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx

Actual performance may differ as a result of end-user environment and application.

Note: Specifications subject to change without notice.


Catalog Number
Notes
Type

6" Finishing Trim

6E1

PREMIUM EYEBALL

Narrow Flange



Specifications


Height: 6-1/2 (16.5)

Lamp opening: 5-7/8 (14.9)

Diameter: 7-5/8 (19.4)

Trim height when used with
Non-IC incandescent rough-in

All dimensions are inches (centimeters) unless otherwise indicated.



ORDERING INFORMATION

For shortest lead times, configure product using **bolded options**.

Example: 6E1

6E1	
Series	Finish
6E1	(blank) White

Accessories: Order as separate catalog number.	
CRT6	6" goof ring, white

Housing Compatibility: Housing and trim ordered separately.			
Application	Source	Maximum wattage	Housing
IC	Incandescent	75 PAR30	LC6, LI6, L7X, L7XR
		65 BR30	
Non-IC	Incandescent	75 PAR30	LP6
		65 BR30	

6E1 6" Premium Eyeball Full Reflector Trim

For BR and PAR reflector lamps, see lamp manufacturer's published raw lamp data for photometrics.