



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 666RT 2-1/2" RT Emt Comp Coupling *Crouse-Hinds*

|                  |  |
|------------------|--|
| Catalog Number   | 666RT  |
| Manufacturer     | Crouse-Hinds   |
| Description      | Emt Compression Coupling, 2-1/2 In Trade Size, Zinc Plated, 1.88 LB/Ea |
| Weight per unit  | 1.9 (lbs/each)   |
| Product Category | Steel Compression Emt CPLG   |

### Features

|            |                                   |
|------------|-----------------------------------|
| dimensions | 4.5600 IN X 3.3400 IN X 1.3800 IN |
|------------|-----------------------------------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 2-1/2" RT EMT COMP COUPLING  |
| extra long description | MIDWEST 666RT 2 1/2 EMT CMP CPL RAI  |
| Features               | Crouse-Hinds series raintight EMT connectors and couplings are used in raintight environments to join EMT conduit to a box or enclosure, or to couple two ends of EMT conduit. The design prevents water seepage into the conduit, box or enclosure. |

### Manufacturer Information

|       |                           |
|-------|---------------------------|
| Brand | EATON CROUSE-HINDS SERIES |
| GTIN  | 00784564004529            |
| UPC   | 784564004529              |

### Taxonomies, Classifications, and Categories

|                      |                                |
|----------------------|--------------------------------|
| Category Description | STEEL EMT FITTINGS             |
| Type                 | Raintight compression coupling |

### Trade Size

|            |          |
|------------|----------|
| Trade Size | 2-1/2 IN |
|------------|----------|

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 2    |
| Weight Per each | 1.88 |

### Uses, Certifications, and Standards

|          |         |
|----------|---------|
| standard | UL, cUL |
|----------|---------|