

Eaton 7501LA

Catalog Number: 7501LA

Eaton standard grade decorator switch, #14-12 AWG, 15A, Flush, 120/277V, Back/push, Decorator, Maintained, Light almond, Motor Control, Fan, LED, Incand, ELV,MLV,CFL, Florscnt, Halogen, Single-pole, Thermoplastic



General specifications

Product Name	Catalog Number
Eaton standard grade decorator switch	7501LA
UPC	Product Length/Depth
032664627538	1.44 in
Product Height	Product Width
4.19 in	0.97 in
Product Weight	Compliances
0.001 lb	RoHS Compliant
	NAFTA
Certifications	
cULus Listed	

Product specifications

Switch type

Single-pole

Phase

Single-phase

Load type

INC

FLR

LED

CFL

ELV

Fan

HAL

MLV

Motor Control

Closure type

Maintained

Color

Light almond

Wiring method

Back and push

Material

Thermoplastic

Mounting method

Flush

Allowable wire size

#14-12 AWG

Amperage Rating

15A

Number Of Poles

Single-pole

Type

Switch decorator

Voltage rating

120/277 V

Actuator

Decorator

Resources

Brochures

[Decorator standard grade switches spec sheet](#)

Specifications and datasheets

[Eaton Specification Sheet - 7501LA](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)